

## Fixtures with LED



### VT-8013

#### HIGHLIGHTS :

WATTS



10

EQ. WATTS



50

LUMINOUS



800

BEAM ANGLE



110

Item No	: VT-8013
SKU Code	: 4987
Watts	: 10
EQ Watts	: 50
Voltage	: 200-240V,50Hz
Lumen(lm)	: 800
Color Temperature	: 3000K
Beam Angle	: 110
PF	: >0.9
LED Chip Type	: SMD
CRI	: >80
Energy rating label	: A+
Certification	: CE,EMC,ROHS
IP Rating Protection Class	: IP20
Body type	: ALUMINUM+PLASTIC
Dimmable	: No
Life Time	: >20000 Hours
Operation Temperature	: -25 ~50°C
EAN code	: 3800157601955
Unit size	: 300 x 75 x 25mm
Packing details	: 20
Unit cbm	: 0.000881

#### PRODUCT FEATURES

- Cost effective, safe retro fit for T8 Tubes
- Perfectly matches with the traditional daylight tube fixture
- Long Lifespan, Low maintenance and energy saving
- Available in 60 cm, 120 cm, 150 cm & 180 cm
- Widely used for Domestic and Commercial Lighting, Offices, Supermarkets, Shops, Hotels & similar environment

CLICK HERE  
FOR OTHER RELATED CERTIFICATES 