

Outdoor Series



VT-728

HIGHLIGHTS :

WATTS



15

EQ. WATTS



NA

LUMINOUS



1200

BEAM ANGLE



30

Item No	: VT-728
SKU Code	: 7044
Watts	: 15
Base / holder	: E27
Lumen(lm)	: 1200
Beam Angle	: 30
PF	: >0.5
LED Chip Type	: SMD
CRI	: >80
IP Rating Protection Class	: IP65
Body type	: ABS
Dimmable	: No
EAN code	: 3800157606332
Unit size	: 470 x 85 x 85mm
Packing details	: 12
Unit cbm	: 0.003396

PRODUCT FEATURES

- Perfect replacement for traditional fittings as they are more flexible & efficient
- Works perfectly in extreme temperatures from -20° to 50 without any adverse effects
- Specifically designed for Outdoor use
- IP65/67 Protection Rating to ensure safety
- Used for Gardens, Outdoor Residential Areas, Walkways & Passages, Driveways, Fountains, Lawns, Entrance, Patio or Terrace and similar environments

[CLICK HERE FOR OTHER RELATED CERTIFICATES](#) 