

Fixtures with LED



VT-1273

HIGHLIGHTS :

WATTS



14

EQ. WATTS



28

LUMINOUS



1260

BEAM ANGLE



141

Item No	: VT-1273
SKU Code	: 6172
Watts	: 14
EQ Watts	: 28
Voltage	: 200-240V,50/60Hz
Lumen(lm)	: 1260
Color Temperature	: 3000K
Beam Angle	: 141
PF	: >0.9
LED Chip Type	: SMD
CRI	: >80
Energy rating label	: A+
Certification	: CE,EMC,ROHS
IP Rating Protection Class	: IP20
Body type	: PLASTIC
Dimmable	: No
Life Time	: >20000 Hours
Operation Temperature	: -25 ~50°C
EAN code	: 3800230629210
Unit size	: 1200 x 25mm
Packing details	: 50
Unit cbm	: 0.0015

PRODUCT FEATURES

- Cost effective, safe retro fit for T8 Tubes
- Perfectly matches with the traditional daylight tube fixture
- Long Lifespan, Low maintenance and energy saving
- Available in 60 cm, 120 cm, 150 cm & 180 cm
- Widely used for Domestic and Commercial Lighting, Offices, Supermarkets, Shops, Hotels & similar environment

CLICK HERE
FOR OTHER RELATED CERTIFICATES 