

LED Strip Lights



VT-5050 30

HIGHLIGHTS :

WATTS



4.8

EQ. WATTS



NA

LUMINOUS



420

BEAM ANGLE



120

Item No	: VT-5050 30
SKU Code	: 2144
Watts	: 4.8
Voltage	: 12V
Lumen(lm)	: 420
Color Temperature	: 5500K-6000K
Beam Angle	: 120
Energy rating label	: A
Certification	: CE,EMC,ROHS
IP Rating Protection Class	: IP65
Dimmable	: No
Life Time	: >20000 Hours
Operation Temperature	: -25 ~50°C
EAN code	: 3800230621399
Unit size	: 10mm
Packing details	: 100
Unit cbm	: 0.0002

PRODUCT FEATURES

- Flexible & easy installation
- Exceptionally low power consumption
- Available in 1 or 1.5 meter rigid bar options with different options of Aluminium Profiles
- Ideal for illuminating Borders, Edges, Cabinets, Bars and any area with limited space for installation
- Safe to use in most of the application areas like Kitchens, Bathroom,Cabinet and so on.

CLICK HERE
FOR OTHER RELATED CERTIFICATES 