


## LED Strip Lights



### HIGHLIGHTS :

WATTS



4.8

EQ. WATTS



NA

LUMINOUS



0

BEAM ANGLE



NA

SKU Code	: 2352
Watts	: 4.8
Voltage	: 12V
Lumen(lm)	: 0
Color Temperature	: RGB
Energy rating label	: A
Certification	: CE,EMC,ROHS
Dimmable	: No
Life Time	: >20000 Hours
Operation Temperature	: -25 ~50°C
EAN code	: 3800230621658
Packing details	: 0
Unit cbm	: 0.004719

### PRODUCT FEATURES

- Flexible & easy installation
- Exceptionally low power consumption
- Available in 1 or 1.5 meter rigid bar options with different options of Aluminium Profiles
- Ideal for illuminating Borders, Edges, Cabinets, Bars and any area with limited space for installation
- Safe to use in most of the application areas like Kitchens, Bathroom,Cabinet and so on.

CLICK HERE  
FOR OTHER RELATED CERTIFICATES 