

LED Downlights



VT-26451

HIGHLIGHTS :

WATTS



40

EQ. WATTS



350

LUMINOUS



4800

BEAM ANGLE



120

Item No	: VT-26451
SKU Code	: 1279
Watts	: 40
EQ Watts	: 350
Base / holder	: RECESSED
Voltage	: 220-240V,50Hz
Lumen(lm)	: 4800
Color Temperature	: 4000K
Beam Angle	: 120
Commercial type	: ROUND
PF	: >0.9
LED Chip Type	: COB
CRI	: >80
Energy rating label	: A++
Certification	: CE,EMC,ROHS
IP Rating Protection Class	: IP20

Body type	: PKW
Dimmable	: No
Life Time	: >20000 Hours
Operation Temperature	: -25 ~50°C
EAN code	: 3800157612012
Unit size	: D:220x103MM
Cutting size	: D:207mm
Packing details	: 12
Unit cbm	: 0.00759

PRODUCT FEATURES

- Innumerable styles & Elegant appearance
- Non - Flickering
- No UV Radiation
- Premium Quality Power Driver with lowest power factor saver & high RA
- Varied finishes with strong die cast Aluminium body
- Residences, Showrooms, Hotels & Boutiques etc.

[CLICK HERE](#)
FOR OTHER RELATED CERTIFICATES