

LED Spotlights



VT-2886

HIGHLIGHTS :

WATTS



7

EQ. WATTS



75

LUMINOUS



550

BEAM ANGLE



38

Item No	:	VT-2886
SKU Code	:	1668
Watts	:	7
EQ. Watts	:	75
Base / holder	:	GU10
Voltage	:	220-240V,50Hz
Lumen(lm)	:	550
Color Temperature	:	6000K
Beam Angle	:	38
PF	:	>0.5
LED Chip Type	:	SMD
CRI	:	>80
Energy rating label	:	A+
Certification	:	CE,EMC,ROHS
IP Rating Protection Class	:	IP20
Body type	:	PLASTIC
Dimmable	:	Yes
Life Time	:	>20000 Hours
Operation Temperature	:	-25 ~50°C
EAN code	:	3800157602099
Unit size	:	D:50x57mm
Packing details	:	200.00
Unit cbm	:	0.00020

PRODUCT FEATURES

- Lasts 20 times longer than Standard Bulbs
- Uses 80% less energy than Standard Bulbs
- Non – Flickering
- Excellent Heat Radiation Efficiency
- Customized exterior for stronger body
- Perfect choice for Exhibition Stands,Hotels, Bars, Commercial & Residential Lighting