

LED Spotlights



VT-2778

HIGHLIGHTS :

WATTS



7

EQ. WATTS



45

LUMINOUS



500

BEAM ANGLE



110

Item No	:	VT-2778
SKU Code	:	1672
Watts	:	7
EQ. Watts	:	45
Base / holder	:	GU10
Voltage	:	220-240V,50Hz
Lumen(lm)	:	500
Color Temperature	:	3000K
Beam Angle	:	110
PF	:	>0.5
LED Chip Type	:	SMD
CRI	:	>80
Energy rating label	:	A+
Certification	:	EMC,LVD,ROHS
IP Rating Protection Class	:	IP20
Body type	:	PLASTIC
Dimmable	:	No
Life Time	:	20,000 HOURS
Operation Temperature	:	-20~50'C
EAN code	:	3800157602136
Unit size	:	D:50x57mm
Packing details	:	200.00
Unit cbm	:	0.00020

PRODUCT FEATURES

- Lasts 20 times longer than Standard Bulbs
- Uses 80% less energy than Standard Bulbs
- Non – Flickering
- Excellent Heat Radiation Efficiency
- Customized exterior for stronger body
- Perfect choice for Exhibition Stands,Hotels, Bars, Commercial & Residential Lighting