

LED Spotlights



VT-1975

HIGHLIGHTS :

WATTS



5

EQ. WATTS



40

LUMINOUS



320

BEAM ANGLE



110

Item No	:	VT-1975
SKU Code	:	1686
Watts	:	5
EQ. Watts	:	40
Base / holder	:	GU10
Voltage	:	220-240V,50Hz
Lumen(lm)	:	320
Color Temperature	:	4500K
Beam Angle	:	110
PF	:	>0.5
LED Chip Type	:	SMD
CRI	:	>80
Energy rating label	:	A+
Certification	:	EMC,LVD,ROHS
IP Rating Protection Class	:	IP20
Body type	:	PLASTIC
Dimmable	:	No
Life Time	:	20,000
Operation Temperature	:	-20~50'C
EAN code	:	3800157606257
Unit size	:	D:50x57mm
Unit cbm	:	0.00030

PRODUCT FEATURES

- Lasts 20 times longer than Standard Bulbs
- Uses 80% less energy than Standard Bulbs
- Non – Flickering
- Excellent Heat Radiation Efficiency
- Customized exterior for stronger body
- Perfect choice for Exhibition Stands,Hotels, Bars, Commercial & Residential Lighting