

LED Spotlights



VT-1977

HIGHLIGHTS :

WATTS



7

EQ. WATTS



45

LUMINOUS



500

BEAM ANGLE



110

| | |
|----------------------------|------------------|
| Item No | : VT-1977 |
| SKU Code | : 1689 |
| Watts | : 7 |
| EQ Watts | : 45 |
| Base / holder | : MR16 |
| Voltage | : AC/DC:12V,50Hz |
| Lumen(lm) | : 500 |
| Color Temperature | : 4500K |
| Beam Angle | : 110 |
| PF | : >0.5 |
| LED Chip Type | : SMD |
| CRI | : >80 |
| Energy rating label | : A+ |
| Certification | : EMC,LVD,ROHS |
| IP Rating Protection Class | : IP20 |
| Body type | : PLASTIC |
| Dimmable | : No |
| Life Time | : 20,000 |
| Operation Temperature | : -20~50'C |
| EAN code | : 3800157606967 |
| Unit size | : D:50x50mm |
| Packing details | : 200 |
| Unit cbm | : 0.000125 |

PRODUCT FEATURES

- Lasts 20 times longer than Standard Bulbs
- Uses 80% less energy than Standard Bulbs
- Non – Flickering
- Excellent Heat Radiation Efficiency
- Customized exterior for stronger body
- Perfect choice for Exhibition Stands,Hotels, Bars, Commercial & Residential Lighting

[CLICK HERE](#)
FOR OTHER RELATED CERTIFICATES