

LED Bulb Series



VT-1861

HIGHLIGHTS :

WATTS



3

EQ. WATTS



25

LUMINOUS



210

BEAM ANGLE



120

Item No	: VT-1861
SKU Code	: 4219
Watts	: 3
EQ Watts	: 25
Base / holder	: E14
Voltage	: 220-240V,50Hz
Lumen(lm)	: 210
Color Temperature	: 2700K
Beam Angle	: 120
Commercial type	: R39
PF	: >0.4
LED Chip Type	: SMD
CRI	: >80
Energy rating label	: A+
Certification	: CE,EMC,ROHS
IP Rating Protection Class	: IP20

Body type	: PLASTIC
Dimmable	: No
Life Time	: >20000 Hours
Operation Temperature	: -25 ~50°C
EAN code	: 3800230625472
Unit size	: D:39x67mm
Packing details	: 200
Unit cbm	: 0.000176

PRODUCT FEATURES

- Lasts 20 times longer than Standard Bulbs
- Uses 80% less energy than Standard Bulbs
- Aluminium & Thermoplastic Body options available
- Non – Flickering
- Widely used in Residential Lighting.
- LED Bulbs are the best replacement for conventional Incandescent or Fluorescent Bulbs
- Smart choice for the conventional look
- Looks are deceptive in this case
- LED innovation made to look like a traditional bulb

[CLICK HERE](#)
FOR OTHER RELATED CERTIFICATES