

## LED PAR Bulb Series



### VT-1212

#### HIGHLIGHTS :

WATTS



12

EQ. WATTS



60

LUMINOUS



750

BEAM ANGLE



40

Item No	: VT-1212
SKU Code	: 4266
Watts	: 12
EQ Watts	: 60
Base / holder	: E27
Voltage	: 220-240V,50Hz
Lumen(lm)	: 750
Color Temperature	: 2700K
Beam Angle	: 40
Commercial type	: PAR30
PF	: >0.5
LED Chip Type	: SMD
CRI	: >80
Energy rating label	: A+
Certification	: CE,EMC,ROHS
IP Rating Protection Class	: IP20

Body type	: PLASTIC
Dimmable	: No
Life Time	: >20000 Hours
Operation Temperature	: -25 ~50°C
EAN code	: 3800230627513
Unit size	: D:95x114mm
Packing details	: 20
Unit cbm	: 0.0014

#### PRODUCT FEATURES

- Lasts 20 times longer than Standard Bulbs
- Uses 80% less energy than Standard Bulbs
- Aluminium & Thermoplastic Body options available
- Non – Flickering
- Widely used in Residential Lighting.
- LED Bulbs are the best replacement for conventional Incandescent or Fluorescent Bulbs
- Smart choice for the conventional look
- Looks are deceptive in this case
- LED innovation made to look like a traditional bulb

[CLICK HERE](#)  
FOR OTHER RELATED CERTIFICATES