

LED Filament Series



VT-1964

HIGHLIGHTS :

WATTS



4

EQ. WATTS



40

LUMINOUS



350

BEAM ANGLE



300

Item No	: VT-1964
SKU Code	: 4361
Watts	: 4
EQ Watts	: 40
Base / holder	: E27
Voltage	: 220-240V,50Hz
Lumen(lm)	: 350
Color Temperature	: 2200K
Beam Angle	: 300
Commercial type	: ST64
PF	: >0.7
LED Chip Type	: FILAMENT
CRI	: >80
Energy rating label	: A+
Certification	: CE,EMC,ROHS
IP Rating Protection Class	: IP20

Body type	: GLASS
Dimmable	: No
Life Time	: >20000 Hours
Operation Temperature	: -25 ~50°C
EAN code	: 3800157602747
Unit size	: D:58x139mm
Packing details	: 50
Unit cbm	: 0.000772

PRODUCT FEATURES

- Lasts 20 times longer than Standard Bulbs
- Uses 80% less energy than Standard Bulbs
- Aluminium & Thermoplastic Body options available
- Non – Flickering
- Widely used in Residential Lighting.
- LED Bulbs are the best replacement for conventional Incandescent or Fluorescent Bulbs
- Smart choice for the conventional look
- Looks are deceptive in this case
- LED innovation made to look like a traditional bulb

[CLICK HERE](#)
FOR OTHER RELATED CERTIFICATES