

LED Bulb Series



VT-1853

HIGHLIGHTS :

WATTS



10

EQ. WATTS



60

LUMINOUS



806

BEAM ANGLE



200

Item No	: VT-1853
SKU Code	: 4443
Watts	: 10
EQ Watts	: 60
Base / holder	: B22
Voltage	: 220-240V,50Hz
Lumen(lm)	: 806
Color Temperature	: 4500K
Beam Angle	: 200
Commercial type	: A60
PF	: >0.5
LED Chip Type	: SMD
CRI	: >80
Energy rating label	: A+
Certification	: CE,EMC,ROHS
IP Rating Protection Class	: IP20

Body type	: THERMAL PLASTIC
Dimmable	: No
Life Time	: >20000 Hours
Operation Temperature	: -25 ~50°C
EAN code	: 3800157607698
Unit size	: D:60x108mm
Packing details	: 200
Unit cbm	: 0.000576

PRODUCT FEATURES

- Lasts 20 times longer than Standard Bulbs
- Uses 80% less energy than Standard Bulbs
- Aluminium & Thermoplastic Body options available
- Non – Flickering
- Widely used in Residential Lighting.
- LED Bulbs are the best replacement for conventional Incandescent or Fluorescent Bulbs
- Smart choice for the conventional look
- Looks are deceptive in this case
- LED innovation made to look like a traditional bulb

[CLICK HERE](#)
FOR OTHER RELATED CERTIFICATES