

Brand Name: Acer
DVI: Yes
Environmentally Friendly: Yes
Green Compliant: Yes
Number of USB 2.0 Ports: 6
Operating System Architecture: 64-bit
Operating System Platform: Windows
Operating System: Windows 7 Professional
Optical Drive Type: DVD-Writer
Processor Manufacturer: Intel
Processor Model: i5-4460
Processor Speed: 3.20 GHz
Processor Type: Core i5
Product Family: Extensa M2610
Product Type: Desktop Computer
Standard Memory: 4 GB
Total Hard Drive Capacity: 500 GB
Total Number of USB Ports: 6
VGA: Yes

Display & Graphics

Maximum Memory: 16 GB
TV Card: No

General Information

Brand Name: Acer
Manufacturer Part Number: DT.X0CEK.018
Manufacturer Website Address: <http://www.acer.co.uk>
Manufacturer: Acer, Inc
Package Contents:

- Extensa M2610 Desktop Computer
- USB Keyboard
- USB Mouse

Product Line: Extensa
Product Name: Extensa M2610 Desktop Computer
Product Series: M2610
Product Type: Desktop Computer

I/O Expansions

Number of PCI Express x1 Slots: 2
Number of PCI Express x16 Slots: 1
Number of PCI Slots: 1
Number of Total Expansion Slots: 4

Input Devices

Keyboard Type: Physical Keyboard
Keyboard: Yes
Pointing Device Type: Mouse

Interfaces/Ports

Audio Line In: Yes
Audio Line Out: Yes
DVI: Yes
Ethernet Technology: Gigabit Ethernet
Modem (RJ-11): No
Modem: No
Network (RJ-45): Yes
Number of USB 2.0 Ports: 6
Total Number of USB Ports: 6
VGA: Yes

Keyboard/Keypad

Keyboard Type: Physical Keyboard

Media & Performance

Ethernet Technology: Gigabit Ethernet

Memory

Maximum Memory: 16 GB
Memory Card Reader: No
Memory Standard: DDR3-1600/PC3-12800
Memory Technology: DDR3 SDRAM

Standard Memory: 4 GB

Miscellaneous

Certifications & Standards:

- DMI
- GS
- PC2001
- CE
- CB

Environmental Certification: RoHS

Environmentally Friendly: Yes

Features: Security Slot

Green Compliance: RoHS

Certificate/Authority:

Green Compliant: Yes

Package Contents:

- Extensa M2610 Desktop Computer
- USB Keyboard
- USB Mouse

Software Included:

- Microsoft® Office Starter: reduced-functionality Word and Excel® only, with advertising. No PowerPoint® or Outlook®. Buy Office 2010 to use the full-featured software.
- Bing™ Bar
- Windows Live™ Essentials

Network & Communication

Ethernet Technology: Gigabit Ethernet

Modem: No

Physical Characteristics

Depth: 372 mm

Height: 365 mm

Width: 175 mm

Pointing Device

Pointing Device Type: Mouse

Power Description

Maximum Power Supply: 220 W

Wattage:

Processor & Chipset

64-bit Processing: Yes

Cache: 6 MB

Chipset Manufacturer: Intel

Chipset Model: H81 Express

Direct Media Interface: 5 GT/s

Hyper-Threading: No

Maximum Turbo Speed: 3.40 GHz

Number of Processors Installed: 1

Number of Processors: 1

Supported:

Processor Core: Quad-core (4 Core)

Processor Manufacturer: Intel

Processor Model: i5-4460

Processor Speed: 3.20 GHz

Processor Type: Core i5

vPro Technology: No

Product Information

Features: Security Slot

Operating System Platform: Windows

Width: 175 mm

Software

Operating System Architecture: 64-bit

Operating System Platform: Windows

Operating System: Windows 7 Professional

Software Included:

- Microsoft® Office Starter: reduced-functionality Word and Excel® only, with advertising. No PowerPoint® or Outlook®. Buy Office 2010 to use the full-featured software.
- Bing™ Bar
- Windows Live™ Essentials

Storage

Features:	Security Slot
Hard Drive Configuration:	1 x 500 GB
Hard Drive Interface:	Serial ATA/300
Hard Drive RPM:	7200
Number of Hard Drives:	1
Optical Drive Type:	DVD-Writer
Optical Media Supported:	DVD-RAM/±R/±RW
Total Hard Drive Capacity:	500 GB

Technical Information

64-bit Processing:	Yes
Direct Media Interface:	5 GT/s
Ethernet Technology:	Gigabit Ethernet
Features:	Security Slot
Hard Drive RPM:	7200
Memory Card Reader:	No
Memory Standard:	DDR3-1600/PC3-12800
Memory Technology:	DDR3 SDRAM
Operating System:	Windows 7 Professional
Optical Drive Type:	DVD-Writer
Optical Media Supported:	DVD-RAM/±R/±RW
Processor Core:	Quad-core (4 Core)
Processor Manufacturer:	Intel

Wireless Specifications

Features:	Security Slot
-----------	---------------