

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0016020069](#)
Status: **Active**
Overview: C-Grid® Products
Description: SL™ Crimp Terminal, Series 70058, Female, with Tin (Sn) Plated Contact, 24-30 AWG, Reel

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	70058
Application	Signal
Comments	Use with CyClone Panel-to-Panel Connector 73099
Crimp Quality Equipment	Yes
Overview	C-Grid® Products
Packaging Alternative	16-02-0096 (Loose)
Product Name	SL™
UPC	800753595941

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.073/g
Packaging Type	Reel
Plating min - Mating	3.810µm
Plating min - Termination	1.905µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52mm max.
Wire Size AWG	24, 26, 28, 30
Wire Size mm²	N/A

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	70058-0004
--------------------	------------

Reference - Drawing Numbers

Sales Drawing	SD-70058-0004
---------------	---------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[70058 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Insertion Tool	0011020022
Hand Crimp Tool For SL™ Crimp Terminals	0638258800
FineAdjust™ Applicator, 24-30 AWG Wire	0639001500
FineAdjust™ Applicator for Female	0639003100

Crimp Terminal,
24-30 AWG Wire
T2 Terminator 0639103100
Tooling Die

Japan

Description **Product #**

Applicator for M211A 0570143000

Bench Press, 22-30

AWG Wire

Side-Feed Applicator 0570143200

For Full-Auto

Machine

Hand Insertion Tool 0570336000

This document was generated on 09/19/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION