

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300390283](#)
Status: **Active**
Overview: Brad® Mini-Change® Connectors
Description: DeviceNet* Mini-Change® Receptacle, 5 Poles, Female (Straight) with DeviceNet* Thick Trunk Cable, 1/2" - 14 NPT Threads, 0.050m (1.97") Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E152210

General

Product Family Industrial Receptacles
 Series [130039](#)
 IP Rating IP67
 NEMA Rating NEMA 6
 Overview [Brad® Mini-Change® Connectors](#)
 Product Name DeviceNet* Trunk, Mini-Change®
 Type Single Ended (pigtail)
 UPC 78678829512

Physical

Coupling Type Internal Thread
 Gender Female
 Keyway Single
 Length 0.050m
 Material - Component Gray Anodized Aluminum
 Mounting Thread Size 1/2" - 14 NPT
 Orientation Straight
 Panel Mount Front
 Poles 5
 Temperature Range - Operating -20°C to +80°C
 Wire Size AWG N/A
 Wire/Cable Type N/A


Electrical

Current - Maximum per Contact 8.0A
 Voltage - Maximum 300V AC/DC

Material Info

Engineering Number DN5000-M005

*DeviceNet is a trademark of Open DeviceNet Vendor Association (ODVA).



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/21/2016 (20 June 2016)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

Search Parts in this Series

[130039](#) Series