

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300540013](#)  
**Status:** **Active**  
**Overview:** Brad® Industrial Ethernet Solutions  
**Description:** Ultra-Lock® (M12) Single-Ended Receptacle, 4 Poles, Female (Straight) to Pigtail, 2.0m (6.56') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E200650

**General**

Product Family Industrial Cordsets  
 Series [130054](#)  
 Connector End A Ultra-Lock® (M12)  
 Connector End B Pigtail  
 IP Rating IP67  
 Overview [Brad® Industrial Ethernet Solutions](#)  
 Performance Category 5e  
 Product Name Ultra-Lock® (M12)  
 Type Single Ended  
 UPC 78678804778

**Physical**

Cable Diameter N/A  
 Cable Length 2.0m (6.56')  
 Color - Cable Jacket Teal  
 Coupling Style Threaded  
 Gender Female-Pigtail  
 Keyway D-coded  
 LED Indicator No  
 Material - Cable Jacket PVC  
 Material - Connector Body PVC  
 Material - Contact Copper  
 Material - Coupling Nut Nickel-plated Brass  
 Material - Plating Mating Gold over Nickel  
 Orientation Straight  
 Poles 4  
 Temperature Range - Operating -25°C to +75°C  
 Wire Size AWG 24  
 Wire/Cable Type E152210

**Electrical**


Current - Maximum per Contact 1.5A  
 Voltage - Maximum 125V

**Material Info**

Engineering Number ERWAAJ4002M020

**Reference - Drawing Numbers**

Sales Drawing SD-130054-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Contained Per - ED/21/2016 (20 June 2016)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

**Search Parts in this Series**

[130054 Series](#)