

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300680079](#)
Status: **Active**
Overview: Brad® Quick-Change® Connectors
Description: Brad® Power Quick-Change® 4 Pole Tee with 4 Pole Quick-Change® Drop

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E258922

General

Product Family Industrial Tees and Splitters
 Series [130068](#)
 IP Rating IP67
 Overview [Brad® Quick-Change® Connectors](#)
 Product Name Quick-Change®
 Type Power Tap Tee
 UPC 78678877118

Physical

Color - Cable Jacket Gray
 Drop Connector Quick-Change®
 Drop Gender Female
 Keyway Single
 Left Trunk Connector Quick-Change®
 Left Trunk Gender Female
 Leg 1 Length N/A
 Leg 2 Length N/A
 Material - Cable Jacket N/A
 Material - Connector Body PVC
 Material - Coupling Nut Anodized Aluminum
 Net Weight 303.907/g
 Poles 4
 Right Trunk Connector Quick-Change®
 Right Trunk Gender Male
 Temperature Range - Operating -20°C to +90°C

Electrical


Current - Maximum per Contact 25.0A
 Voltage - Maximum 600V AC/DC

Material Info

Old Part Number TC40C40-200

Reference - Drawing Numbers

Sales Drawing SD-130068-010



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

Search Parts in this Series

[130068](#) Series