



PCB Terminal Strips with Locking Slides 0.5 mm²

CAGE CLAMP®

Pin spacing: 2.5 mm / 0.098 in.		Pin spacing: 2.54 mm / 0.1 in.	
0.08 ... 0.5 mm ²	28 ... 20 AWG	0.08 ... 0.5 mm ²	28 ... 20 AWG
160 V/2.5 kV/2 6 A	150 V/4 A	160 V/2.5 kV/2 6 A	150 V/4 A



$L = (\text{pole no.} \times \text{pin spacing}) + 1.5 \text{ mm}$

○ A groove at the back of the PCB terminal strip differentiates between the two pin spacings

Pole No.	Item No.	Pack. Unit	Pole No.	Item No.	Pack. Unit
PCB terminal strip with locking slides, 2 solder pins/pole in line, gray, locking slides, white			PCB terminal strip with locking slides, 2 solder pins/pole in line, gray, locking slides, white		
2	218-102	1000 (10 x 100)	2	218-502	1000 (10 x 100)
3	218-103	1000 (10 x 100)	3	218-503	1000 (10 x 100)
4	218-104	500 (5 x 100)	4	218-504	500 (5 x 100)
5	218-105	500 (5 x 100)	5	218-505	500 (5 x 100)
6	218-106	280 (4 x 70)	6	218-506	280 (4 x 70)
7	218-107	240 (4 x 60)	7	218-507	240 (4 x 60)
8	218-108	220 (4 x 55)	8	218-508	220 (4 x 55)
9	218-109	200 (4 x 50)	9	218-509	200 (4 x 50)
10	218-110	180 (4 x 45)	10	218-510	160 (4 x 40)
11	218-111	160 (4 x 40)	11	218-511	160 (4 x 40)
12	218-112	140 (4 x 35)	12	218-512	140 (4 x 35)
13	218-113	140 (4 x 35)	13	218-513	140 (4 x 35)
14	218-114	120 (4 x 30)	14	218-514	120 (4 x 30)
15	218-115	120 (4 x 30)	15	218-515	120 (4 x 30)
16	218-116	100 (4 x 25)	16	218-516	100 (4 x 25)
:	:		:	:	
21	218-121	80 (4 x 20)	21	218-521	80 (4 x 20)
22	218-122	80 (4 x 20)	22	218-522	80 (4 x 20)
23	218-123	80 (4 x 20)	23	218-523	80 (4 x 20)
24	218-124	60 (4 x 15)	24	218-524	60 (4 x 15)

PCB terminal strips in other colors are available upon request (depending on quantity required):

● black
● red
● blue
● orange
● green
○ white

Other pole numbers, direct marking, as well as mixed-color PCB terminal strips are available upon request (depending on quantity required).