

LCD COLOUR MONITOR

Model No. LSM6323

5.6" TFT LCD Colour Monitor with Digital LED Back light Panel, Metal Cased, Carry bag, Straps, Energy saving Rechargeable Li-ion Battery for portable Video solutions. Available in other sizes.



Warning: Do not connect the Charger direct to the monitor or damage will occur.

Main Features:

- Resolution: 960 x 234
- Picture Ratio: 4:3.
- Brightness: 200 cd/m2. LED Back Light.
- Contrast Ratio: 500:1
- LCD Panel Screen Protector.
- Hot keys for V1/2, Image rotation.
- Inputs: Composite Video x 2.
- Carry Bag and Straps.
- Rechargeable Li-ion battery.
- Output: Video and Audio via Speaker.

The LSM6323 with TFT active matrix technology with LED Backlight and up to 7 hours battery life, offering a sharp display with universal application opportunities. Ideal for the “on the move” Video engineer as the monitor comes with Carry Bag with Viewing window and easy clip on Straps for Hands free use. Rechargeable battery pack and video connectors are also supplied. The bag has a cutout at the side for the connections. Other uses are for Surveillance Systems setup, Reverse Monitoring Vehicle systems and Multimedia Video applications. An audio input enables sound to be monitored via speaker or Headphone socket.

SPECIFICATIONS:

- Active area: 114.0 x 85.0 (WxH)mm. • 262K Colours. • PAL and NTSC Auto.
- Response Time: 30ms (Tr/Tf). • Viewing angle: Left/Right: 50°, Up: 30°, Down: 50°.
- Controls: Menu, +, -, Left/Right/Up/Down image reverse, Video 1 & 2, On/off. Power On LED.
- Full OSD: Brightness, Contrast, Hew, Saturation.
- Audio In and Out by Headphone Jack or Speaker. Video Output.
- Power Source: 12V DC, 500mA, 7 Watts approx. AC Charger: 100-240V 50/60Hz 1.5Amps.
- Dimensions: Unit:165 x 134 x 35. Bag: 255 x 65 x 155. Carton: 288 x 63 x 233 (WxHxD)mm.
- Weight: Unit: 0.83Kgms, Bag Complete: 1.32Kgms. Carton:1.84Kgms
- Temp: Operation: 0°C~50°C, Storage: -20~ 60°.

Connections: Input: Video 1 & 2 Phono Socket, Audio Phono Socket. Output: Video Phono Socket. Audio via Headphone Jack: 3.5mm stereo (mono x 2)

Standard accessories: AC Charger UK, Rechargeable Battery, DC Lead, Carry Bag and Straps, RCA-BNC adaptors x 4.

Warning: Do not connect the Charger direct to the monitor or damage will occur.

- All information correct at time of going to press. Design and specification are subject to change without prior notice. E&EO

Product Shop International Ltd

PO Box 5503, Newbury, Berkshire, RG14 6YP. UK

e-mail: sales@productshop.co.uk Website www.productshop.co.uk

Tel: +44 (0) 844 800 4433 Fax: +44 (0) 844 800 9876

Registered office: As above. Registered No. 3852764 VAT No. GB 727 0478 29