


For all your LCD Displays

Psi

LCD COLOUR MONITOR

Model No. LM6323

5.6" Colour TFT LCD with LED Back light, 2 x Composite Video, Video Output, Audio via speaker, Monitor Metal Cased with Sun visor. Other sizes available.



Main Features:

- Resolution: 960 x 234
- Picture Ratio: 4:3
- Brightness: 200 cd/m² LED Back Light.
- Contrast Ratio: 500:1
- Mounting: "C" mount. VESA 75mm.
- LCD Panel Screen Protector.
- Output: Video and Audio via Speaker.
- Aluminium cabinet finished in Black.
- OSD Menu with Hot keys.
- Left/Right/Up/Down image reverse.
- Inputs: 2 x Composite, Audio.

The LM6323 with TFT active matrix technology, offers a sharp and high contrast display with universal application opportunities. With a metal case it provides a rugged unit, Ideal for Surveillance Systems, Reverse Monitoring Vehicle systems and Video applications. Video image reverse Up/Down/Left/Right and Video 1 & 2 hot keys. An audio input enables sound reception via speaker. With Sun Visor Hood and 75mm VESA 75mm Mounting. Note: The stand type may vary.

SPECIFICATIONS:

- Active area: 112.896 x 84.672 (WxH)mm. • Dot Pitch: 0.0588 x 0.1764. • PAL and NTSC Auto.
- Response Time: 10/15ms (Tr/Tf). • Viewing angle: Left/Right: 70°, Up:50°, Down:70°.
- Controls: Menu, +, -, Left/Right/Up/Down image reverse, Video 1 & 2, On/off. Power On LED.
- Audio In/Out and by Headphone Jack and Speaker. Video Output.
- Power Source: 12V DC, 500mAmp, 7 Watts approx.
- Dimensions: 169.4 x 136.2 x 36. Carton: 283 x 233 x 61 (WxHxD)mm.
- Weight: Unit: 0.82Kgms, Carton: 1.66Kgms. • Temp: Operation: -20°C~70°C, Storage: -30~80°C.

Connections: Input: Video 1 & 2 Phono Socket, Audio Phono Socket. Output: Video Phono Socket. Audio via Headphone Jack: 3.5mm.

Standard accessories: Stand, AC Adaptor, Hood Visor.

- All information correct at time of going to press. Design and specification are subject to change without prior notice. E&EO

Product Shop International Ltd

Unit 2 Whitway Farm, Winchester Road, Burghclere, RG20 9LE. UK

e-mail: sales@productshop.co.uk Website www.productshop.co.uk

Tel: +44 (0) 844 800 4433

Registered office: As above. Registered No. 3852764 VAT No. GB 727 0478 29