


# LCD COLOUR MONITOR

## Model No. LM7312

7.0" TFT LCD with LED Back light, PAL & NTSC Colour Video Monitor, 2 x Composite video input, Video Output, Audio output via Speaker, Recessed Metal Cabinet. 4:3 and 16:9 aspect Ratio. Available in other sizes.



### Main Features:

- Resolution: 336960 pixels - 1440 x 234
- Picture Ratio: 4:3 & 16:9
- Brightness: 500 cd/m<sup>2</sup> LED Back Light.
- Contrast Ratio: 300:1
- Inputs: 2 x Composite, Audio.
- LCD Panel Screen Protector.
- Mounting: Recessed Cabinet.
- Output: Video & Audio via rear Headphone
- Aluminium cabinet finished in Black.
- OSD Menu with Hot keys.
- Left/Right/Up/Down image reverse.

The LM7312 with TFT active matrix technology, offers a sharp and high contrast display with universal application opportunities. Recessed Metal cased providing a rugged unit. Easy to setup and adjust with Front panel keys and OSD. Video image Up/Down/Left/Right and Video1/2 hot keys. An audio input enables sound output via headphones and Line out. Ideal for Surveillance Systems, Reverse Monitoring Vehicle systems and Video applications. Note: The buttons are black.

### SPECIFICATIONS:

- Active area: 154.08 x 86.58 (WxH)mm. • Dot Pitch: 0.117 x 0.362. • PAL and NTSC Auto.
- Response Time: 12/18ms (Tr/Tf). • Viewing angle: Left/Right: 60°, Up:40°, Down:60°.
- Controls: Menu, +, -, Left/Right/Up/Down image reverse, Video 1 & 2, On/off. Power On LED.
- Audio In/Out and by Headphone Jack. Video Output.
- Power Source: 12V DC, 500mA, 7 Watts approx.
- Dimensions: 211 x 148 x 36.5. Carton: 283 x 61 x 233 (WxHxD)mm.
- Weight: Unit:0.9Kgms, Carton: 1.54Kgms. • Temp: Operation: -30°C~85°C, Storage: -40~95°C.

**Connections:** Input: Video 1 & 2 Phono Socket, Audio Phono Socket. Output: Video Phono Socket. Audio via Headphone Jack: 3.5mm. DC: 2.1mm socket.

**Standard accessories:** AC Adaptor.

- All information correct at time of going to press. Design and specification are subject to change without prior notice. E&EO

## **Product Shop International Ltd**

PO Box 5503, Newbury, Berkshire, RG14 6YP. UK

e-mail: sales@productshop.co.uk Website www.productshop.co.uk

Tel: +44 (0) 844 800 4433 Fax: +44 (0) 844 800 9876

Registered office: As above. Registered No. 3852764 VAT No. GB 727 0478 29