


LCD COLOUR MONITOR

Model No. LCD80AV

8.0" TFT LCD Colour Monitor, LED Backlight, SVGA, 2 x Composite Video BNC, Audio inputs. PAL & NTSC Auto, 4:3 Aspect Ratio, Speaker. Low current consumption.



Main Features:

- Resolution: 480000 pixels - 800 x 600
- Picture Ratio: 4:3
- Brightness: 250 cd/m2 ~ LED Back Light.
- Contrast Ratio: 500:1
- Inputs: SVGA, 2 x Composite Video BNC, 2 x Audio Phono.
- Mounting: Desk or Wall.
- Full OSD.
- Speaker
- PAL and NTSC Auto.
- Cabinet finished in Black.



The LCD80AV with 8.0" TFT active matrix technology offers Low power consumption with a LED backlight, High Contrast giving a very Sharp bright image. This Monitor has universal applications, such as CCTV, In-vehicle use, Portable on the move and for Audio/Video presentations.

SPECIFICATIONS:

- Active area: 162 x 121.5 (WxH)mm. • 16.7M Colours. • PAL and NTSC Auto.
- Response Time: 25 ms (Tr/Tf). • Viewing angle: Left/Right: 70°, Up: 50° Down 70°.
- Controls: Source, Menu, Down, Up, Power, On Led, I/R, On/Off switch.
- Menu Video: Volume, Contrast, Brightness, Hue, Colour, Sharpness.
- Menu PC: Volume, Auto Tune, Contrast, Brightness, H-Position, V-Position, Clock, Phase.
- Power Source: 12V DC, 500mA, 6 Watts. AC Adaptor: Switch Mode 100-240V 50/60Hz.
- Dimensions: Unit: 200 x 165 x 30. Carton: 260 x 77 x 260 (WxHxD)mm.
- Weight: Unit: 540 gms, Carton: 1.18 Kgms. • Temp: Operation: 0°C~50°C, Storage: -20~70°.

Connections: Video Input 1 & 2: 3.5mm Stereo sockets to Video BNC socket and Audio Phono socket. DC Input: 1.35mm Jack Plug (centre Positive), PC: 15 pin D-Sub connector.

Standard accessories: AC Adaptor, Stand, 3.5mm to BNC/Phono cables x 2.

- All information correct at time of going to press. Design and specification are subject to change without prior notice. E&EO

Product Shop International Ltd

PO Box 5503, Newbury, Berkshire, RG14 6YP. UK
e-mail: sales@productshop.co.uk Website www.productshop.co.uk
Tel: +44 (0) 844 800 4433 Fax: +44 (0) 844 800 9876
Registered office: As above. Registered No. 3852764 VAT No. GB 727 0478 29