

GP Batteries

PRODUCT SPECIFICATION

**GP Portable PowerBank
Model : FP10M**

Revision History

Revision	Date	Initiator	Reason for Change
0.0	22 May 2015	Keness Wong	New release

Prepared By Keness Wong	Approved By Patrick Lee
Date: 22 May 2015	Date: 22 May 2015


GPI International Limited

Gold Peak Building, 8/F, 30 Kwai Wing Road,
Kwai Chung, New Territories, Hong Kong.
Tel: (852) 2484 3333 Fax: (852) 24805912
Email: gpii@goldpeak.com
Website: <http://www.gpbatteries.com>

GP Batteries

Product Specification

Model no.: FP10M



Micro USB Charging Cable
(Input / Output)

Product Name	: GP Portable PowerBank FP10M
Description	: Back up power for USB powered electronic devices (e.g. smartphones, tablet PCs)
Battery Rating	: Lithium polymer 3.7V 10000mAh 37.0Wh
Input	: 2A / 5V DC
Output	: OUT 1 : 2.1A / 5V DC OUT 2 : 1.0A / 5V DC Total 3.1A, 2 outputs
Application	: Charge USB powered electronic devices
Recharging Time	: 8 hours (approx.) by 5V/2A ;
Discharging Time	: 2 hours (approx.) 2 outputs full load at the same time (The discharging time may vary for different devices)
Operation Temperature	: 5°C to 40°C
Safety protection	: 1) Over and under temperature protection 2) Over current protection 3) Over charging protection 4) Over discharging protection 5) Short circuit protection

GP Batteries

Product Specification

Model no.: FP10M

LED Indication :

Charging & Discharging the Portable PowerBank

Table 1

Charging & Discharging condition	LED indicator
Charging	Last LED slow flashing
Discharging	Refer to battery status (Table 2)
Fully charged	All On in Green
Errors	Red LED fast flashing

Press button to show battery status :

Table 2

Battery Strength	LED indicator
Good	Four LED on
Good to average	First three LED on
Average	First two LED on
Weak	One LED on
Very Weak	One LED fast flashing
No Power	No LED

Dimensions : 148 (L) x 75.5 (W) x 14 (H) mm

Weight : 283g +/- 5g (approx.)

Certification : CE, FCC, UN38.3

Warranty Period : 12 months from ex-factory date