

For all your LCD Displays

Psi

LCD COLOUR MONITOR

Model No. AN5601B

5.6" TFT LCD Colour Monitor, LED Back Light, PAL & NTSC, 4:3 Aspect Ratio, 2 Video/Audio inputs, Voltage Range 9-36VDC, Wall, Desk, Ceiling mountable. Easy to use front controls, Image reverse, Easy Mini Din connection, Speaker. E13 Certificate.



Main Features:

- Resolution: 960 x 234 ~ 224,640 pixels
- Picture Ratio: 4:3
- Brightness: 330 cd/m² LED Back Light.
- Contrast Ratio: 300:1
- Inputs: 2 x Composite Video, Audio.
- Full OSD and V1/V2 Hot key.
- Easy connecting Mini Din lead.
- Stand for Wall, Ceiling or Desk mounting.
- Cabinet finished in Black.
- Image reverse: Left/Right/Up/Down.
- Audio via Speaker. • Sun Visor
- V2 activation for Reversing Systems.

The AN5601B with TFT active matrix technology and LED Back Light, Slim Line model with On-Screen Display, offering a sharp and high contrast display with wide viewing angle. Easy to use front controls. 2 x Video/Audio inputs and Quick connection via Mini din lead. Audio via Speaker. It has universal application potential and is ideal for Surveillance Systems, Reverse Monitoring Vehicle Systems and Multimedia Video applications. Rear sliding bracket for Wall, Desk or Ceiling mounting.

SPECIFICATIONS:

- Active area: 113.28 x 84.708 (WxH)mm. • PAL and NTSC Auto.
- Response Time: 25ms (Tr/Tf). • Viewing angle: Left/Right: 65°, Up: 45°, Down: 65°.
- Controls: Video 1/2, Down, Up, Menu, Power On/Off, Standby LED.
- OSD: Volume, Brightness, Contrast, Saturation, Hue, Mirror, Power On speed, Default.
- Power Source: Range 9 ~ 36 V DC, 12V DC, 340mA, 4 Watts approx.
- Dimensions: Unit: 148 x 114 x 30. With Visor: 151x70 (WxD) Carton: 180x90x170 (WxHxD)mm
- Weight: Unit: 0.33Kgms, Carton: 0.87Kgms. • Temp: Operation: -20~85°C, Storage: -20~ 85°C.

Connections: Fly lead to 8 pin Mini Din Plug. Lead: 8 pin Mini Din Socket to: Video: 1/2 Phono sockets. Audio: 1/2 Phono sockets, DC 2.1mm Socket. Centre positive. In-Line Fuse: 1¼", 2.5 Amp quick blow. Single wire for V2 activation (for Reversing systems): To Activate Plus 9-36 volts.

Standard accessories: Stand, 2 meter 8 pin Mini Din Lead, Sun shield.

Optional accessories: I/R Remote Control, 8 pin Mini Din Extension lead - 2 mtrs.

- All information correct at time of going to press. Design and specification are subject to change without prior notice. E&EO

Product Shop International Ltd

Unit 2 Whitway Farm, Winchester Road, Burghclere, RG20 9LE. UK

e-mail: sales@productshop.co.uk Website www.productshop.co.uk

Tel: +44 (0) 844 800 4433

Registered office: As above. Registered No. 3852764 VAT No. GB 727 0478 29