


# LCD COLOUR MONITOR

## Model No. L70HV

7.0" TFT LCD FULL HD Colour Video Monitor, LED Back Light, Inputs of HDMI 1080P, VGA, Composite video and Audio. Plastic Cased. PAL / NTSC Auto, Stand for Wall/Desk Mount. I/R Remote. Speaker. 12~24volts. Full OSD. Low current operation. Auto start when Power connected.



### Main Features:

- Resolution: 384,000 pixels, 800 x3RGBx 480
- Picture Ratio: 16:9 and 4:3.
- Brightness: 400 cd/m2. LED Back Light.
- Contrast Ratio: 500:1
- Inputs: HDMI, VGA, Composite Video, Audio.
- Full OSD.
- Mounting: Stand Wall and Desk "C" mount
- Cabinet finished in Black.
- Speaker output: 1 x 1 watt
- Infra-Red Remote control.
- AC adaptor.

The L70HV monitor with TFT active matrix technology, offers a sharp and high contrast display with universal application opportunities. LED backlight for low power. With Inputs of HDMI, VGA, Composite Video and Audio. Mounting via Stand for Wall or Desk, "C" mount. Easy to setup and adjust with Full OSD. An audio input enables sound output via speaker. Ideal for Studio applications, Vehicle systems and High quality Video applications.

### SPECIFICATIONS:

- Active area: 154.08 x 85.92 (WxH)mm. • Colour 16.7M • PAL and NTSC Auto.
- Response Time: 10/15 ms (Tr/Tf). • Viewing angle: Left/Right: 70°, Up:50°, Down 70°.
- HDMI Format: 720P@50/60Hz, 1080I@50/60Hz, 1080P@50/60Hz.
- Controls/Indicators: Mode, Down, Up, Power. On LED, I/R Sensor.
- OSD: Volume, Contrast, Brightness, Hue, Saturation, Sharpness, R,G,B. Restore.
- Power Source: 12~24V DC, 500 mA, 6 Watts approx.
- Dimensions: Unit: 180 x 120 x 23. Carton: 260 x 68 x 240 (WxHxD)mm.
- Weight: Unit: 0.48 Kgms, Carton: 1.01 Kgms. • Temp: Operation: -10°C~60°C, Storage: -30~70°.

**Connections:** Input: HD: HDMI socket, VGA: 15 pin Sub-D, Composite Video In: BNC Socket, Audio In: Phono Socket. Power: 1.3mm DC Jack socket.

**Standard accessories:** AC Adaptor, Wall/Desk Stand, AV Cable, I/R remote control.

**Optional:** Sun shield.

- All information correct at time of going to press. Design and specification are subject to change without prior notice. E&EO

## Product Shop International Ltd

Unit 2 Whitway Farm, Winchester Road, Burghclere, RG20 9LE. UK

e-mail: sales@productshop.co.uk Website www.productshop.co.uk

Tel: +44 (0) 844 800 4433

Registered office: As above. Registered No. 3852764 VAT No. GB 727 0478 29