



For all your LCD Displays

Psi

LCD COLOUR MONITOR

Model No. L80AP

8.0" TFT LCD Colour Video Monitor with LED Back Light, Stylish Slim Line Cabinet. HDMI, PC, Composite Video with BNC connector, Audio In and Out via speaker. I/R Remote control. Full OSD. 12volts. Low current operation. Auto start when Power connected to remembered input. Full Screen mode converts 4:3 to full screen image. Optional: Sun Visor.



Main Features:

- Resolution: 1024 x 600
- Picture Ratio: 17:10, 4:3 and Full Screen.
- Brightness: 500 cd/m2 - LED Back Light.
- Contrast Ratio: 700:1
- Inputs: HDMI, PC, Composite BNC, Audio.
- Outputs: Audio via speaker.
- Mounting: Bottom & Rear "C" Mount, Stand for Desk or Wall mounting.
- Cabinet finished in Black.
- Speaker: 1 x 2 Watts max.

The L80AP is a stylish wide screen monitor with an LED Backlit panel coupled with a high Contrast ratio gives crystal clear images with pure colour definition and depth of field! Boasting HDMI, PC, Composite video via BNC and Audio In/Out via speakers this is truly a versatile monitor for a variety of applications. Mounting options include a Desk Stand and Wall mounting via a bottom and rear 'C' Mount. Infra- Red Remote control included. The L80AP is encased in a smart slim line and durable cabinet making it the "go to" 8" monitor for a variety of applications.

SPECIFICATIONS:

- Active area: 176.64 x 99.36 (WxH)mm. • 16.2M Colours. • PAL and NTSC Auto.
- Response Time: 10/20ms (Tr/Tf). • Viewing angle: Left/Right: 75°, Up 70° Down 75°.
- Controls/Indicators: I/R sensor, On LED, Power, Up, Down, Select, Menu, Source.
- Power Source: 12V DC, 0.67 Amp, 8 Watts approx. AC Adaptor: 100-240V 50/60Hz 1Amp.
- Dimensions: 210 x 151 x 35.6 Carton: 265 x 80 x 260 (WxHxD)mm.
- Weight: Unit: 0.52 Kgms, Carton: 1.2 Kgms. • Temp: Operation: 0~40°C.

Connections: HDMI Input: HDMI Socket, PC: 15 pin Sub-D socket. Composite Video In: BNC. Audio L & R In: 3.5mm stereo jack socket. (Audio Lead: 3.5mm Stereo Jack plug to BNC x 2 sockets). USB: For Service use only. DC input: 2.1mm socket.

Standard accessories: AC adapter, I/R Remote Control, Audio Lead. Desk/Wall stand.

Optional: Sun Visor or VESA 75mm Plate.

- All information correct at time of going to press. Design and specification are subject to change without prior notice. E&EO

Product Shop International Ltd

Unit 2 Whitway Farm, Winchester Road, Burghclere, RG20 9LE. UK

e-mail: sales@productshop.co.uk Website www.productshop.co.uk

Tel: +44 (0) 844 800 4433

Registered office: As above. Registered No. 3852764 VAT No. GB 727 0478 29