



# LCD COLOUR MONITOR

## Model No. L101AP

10.1" TFT LCD Colour Video Monitor with LED Back Light, Stylish Slim Line Cabinet. HDMI, PC, Composite Video with BNC connector, Audio In and Out via speaker. I/R Remote control. Full OSD. 12volts. Low current operation. Auto start when Power connected to remembered input. Full screen mode converts 4:3 to Full screen image. Optional Sun Visor.



### Main Features:

- Resolution: 1280 x 800 - WXGA
- Picture Ratio: 16:10, 4:3 and Full Screen.
- Brightness: 350 cd/m2 - LED Back Light.
- Contrast Ratio: 800:1
- Inputs: HDMI, PC, Composite BNC, Audio.
- Outputs: Audio via speaker.
- Mounting: Bottom & Rear "C" Mount, Stand for Desk or Wall mounting.
- Cabinet finished in Black.
- Speaker: 1 x 2 Watts max.

The L101AP is a Stylish Wide Screen Monitor with TFT technology, offers Professional sharp images and with high contrast ratio 800:1 and Brightness 350 cd/m2 gives superb pictures. With HDMI, PC and Composite video with BNC Connector, Audio In and Out via speakers making it a truly versatile Monitor. Mounting options offer a Stand for Desk and Wall mounting with Bottom and Rear "C" mount. Infra-Red remote control. All mounted in a Smart Slim line tough housing. This compact unit is ideal for Multimedia Video, Surveillance and General purpose systems applications.

### SPECIFICATIONS:

- Active area: 216.96 x 135.6 (WxH)mm. • 16.2M Colours. • PAL and NTSC Auto.
- Response Time: 10/15ms (Tr/Tf). • Viewing angle: Left/Right: 85°, Up/ Down 85°.
- Controls/Indicators: I/R sensor, On LED, Power, Up, Down, Select, Menu, Source.
- Power Source: 12V DC, 0.67 Amp, 7 Watts approx. AC Adaptor: 100-240V 50/60Hz 1Amp.
- Dimensions: 253 x 178 x 34.7. Carton: 335 x 285 x 109 (WxHxD)mm.
- Weight: Unit: 0.53 Kgms, Carton: 1.2 Kgms. • Temp: Operation: 0~40°C.

**Connections:** HDMI Input: HDMI Socket, PC: 15 pin Sub-D socket. Composite Video In: BNC. Audio L & R In: 3.5mm stereo jack socket. (Audio Lead: 3.5mm Stereo Jack plug to BNC x 2 sockets). USB: For Service use only. DC input: 2.1mm socket.

**Standard accessories:** AC adapter, I/R Remote Control, Audio Lead. Desk/Wall stand.

**Optional:** Sun Visor or VESA 75mm Plate.

- All information correct at time of going to press. Design and specification are subject to change without prior notice. E&EO

## Product Shop International Ltd

Unit 2 Whitway Farm, Winchester Road, Burghclere, RG20 9LE. UK

e-mail: sales@productshop.co.uk Website www.productshop.co.uk

Tel: +44 (0) 844 800 4433

Registered office: As above. Registered No. 3852764 VAT No. GB 727 0478 29