


**For all your LCD Displays**

**Psi**

# LCD COLOUR MONITOR

## Model No. LRM6531

3 Monitors x 5.6" TFT LCD with Colour Digital LED Backlight Panel, PC, Composite Video BNC with Loop through - Metal Cased in 19" Rack Mounting. Other sizes available.



### Main Features:

- Resolution: 640 x RGB x 480
- Picture Ratio: 4:3
- Brightness: 200 cd/m<sup>2</sup> LED Back Light.
- Contrast Ratio: 500:1
- Input: PC, Composite Video. BNC.
- Video Output on each Monitor. BNC
- LCD Panel Screen Protector.
- Full OSD and Hot keys.
- Metal Cabinet finished in Black.
- Mounting: 19" Rack Mounting.
- Single Power connection.
- Rack Tilt 30/30°.
- VESA DDC2B and DPMS.

The LRM6531 offers 3 Monitors of 5.6" TFT LCD in one rugged 19" rack mounting 3U high. With Digital panel, Active Matrix technology and LED Backlight it offers a superb sharp and high contrast images. Individual On/Off switch and Full OSD with Hot keys. PC and Composite Video input and outputs (loop through). 12volt operation via single power source. With universal application potential, the unit is ideal for surveillance systems, monitoring systems and multimedia video applications.

### SPECIFICATIONS:

- Active area: 112.896 x 84.672 (WxH)mm. • 16.2M Colours. • PAL and NTSC Auto.
- Response Time: 10/15ms (Tr / Tf). • Viewing angle: Left/Right: 70°, Up: 50°. Down: 70°.
- Controls: Menu, +, -, Up/Down image reverse, Video 1/2, On/Off, with On LED.
- Dot Pitch: 0.0525 x 0.1575 (WxH)mm.
- Power Source: 12 VDC, 660mA, 21Watts approx. AC Adaptor: 100-240V 50/60Hz 1.5Amps.
- Dimensions: 489 x 132.23 x 66. 19" Rack by 3U High. Carton: 510 x 215 x 180. (WxHxD)mm.
- Weight: Unit: 2.3 Kgms, Carton: 3.35 Kgms. • Temp: Operation: -10°C~60°C, Storage: -20~ 70°.

**Connections:** PC: 15 pin D-sub. Video In/Out: BNC. DC input: 2.1mm socket. AC adaptor: IEC socket.

**Standard accessories:** AC adapter, AC Mains Lead.

- All information correct at time of going to press. Design and specification are subject to change without prior notice. E&EO

## Product Shop International Ltd

Unit 2 Whitway Farm, Winchester Road, Burghclere, RG20 9LE. UK

e-mail: sales@productshop.co.uk Website www.productshop.co.uk

Tel: +44 (0) 844 800 4433

Registered office: As above. Registered No. 3852764 VAT No. GB 727 0478 29