

For all your LCD Displays

Psi

LCD COLOUR MONITOR


Model No. LRM1912

19.1" TFT LCD Colour Video Monitor mounted in a 19" Rack Metal Cabinet with Tilt, LED Back Light, inputs of PC, Composite and Y/C (S-Video). Options: Touch screen. Other sizes available.



Main Features:

- Resolution: 1310720 pixels-1280 x 1024
- Picture Ratio: 4:3
- Brightness: 450 cd/m2 LED Back Light.
- Contrast Ratio: 1000:1
- Inputs: PC, Composite, S-Video.
- Mounting: 19" Rack with Tilt.
- Easy to use front controls.
- Metal robust cabinet finished in Black.
- Full OSD menu.



The LRM1912 with TFT technology and LED Back Light, offers a sharp and high contrast ratio of 1000:1. The unit is mounted in a 9U high rugged metal 19" Rack mount housing with tilt and is also suitable for recessed applications. With SXGA, S-Video Y/C) and Composite Video inputs Easy to use front controls with Pixel clock and Phase for optimal image making it a truly versatile monitor. The unit is ideal for Surveillance systems and Multimedia Video applications.

SPECIFICATIONS:

- Active area: 376.3 x 301.0 (WxH)mm. • 16.7M Colours. • PAL and NTSC Auto.
- Response Time: 5/5ms (Tr / Tf). • Viewing angle: Left/Right: 75°, Up/ Down 70°.
- Front control/Indicators: Auto, Up, On LED, Power, Down/Input select, Menu, On/Off switch.
- Menu Functions: Brightness, Contrast, Colour, Saturation, Sharpness.
- Power Source: 12V DC, 1.47 Amp, 17.6 Watts approx. AC Adaptor: 100-240V 50/60Hz 1.5Amps.
- Dimensions: 483 x 400 x 53. Unit: 9U High. Carton: 540 x 185 x 540 (WxHxD)mm.
- Weight: Unit: 6.33 Kgms, Carton: 8.79 Kgms. • Temp:Operation: 0°C~50°C, Storage: -20~ 60°C.

Connections: PC 15 pin Sub-D, Y/C (S-Video): 4 pin mini din socket, Composite Video: Phono socket. DC input: 2.1mm socket. AC adaptor: IEC socket.

Standard accessories: AC adapter, AC Mains Lead, PC Lead, S-Video Lead, Video Lead.

- All information correct at time of going to press. Design and specification are subject to change without prior notice. E&EO

Product Shop International Ltd

Unit 2 Whitway Farm, Winchester Road, Burghclere, RG20 9LE. UK

e-mail: sales@productshop.co.uk Website www.productshop.co.uk

Tel: +44 (0) 844 800 4433

Registered office: As above. Registered No. 3852764 VAT No. GB 727 0478 29