



CAMBLOCK PLUS

PCB
TERMINAL
BLOCKS

5mm pitch Triple Decker Terminal Blocks

- Triple decker terminals
- Moulded in green UL94-V0 flame retardant PA66
- 1.5mm² (30-14AWG)
- Professional rising clamp terminals
- Guided pin alignment
-   approved

CTBPTDVG



SPECIFICATION

| | |
|---------------------------|-------------------------------|
| Rating | 15A/300V |
| Insulation resistance | 500M Ω /500V |
| Withstand Voltage | AC2000V/1min |
| Contact Resistance | 20m Ω (max) |
| Working Temperature | -40°C to 105+°C |
| Mouldings | UL94-V0 Flame retardant PA66 |
| Pin/Terminal | Tin plated brass |
| Rising Clamp | Brass, nickel plated |
| Screw/Torque | M2.5 Steel, zinc plated 0.4Nm |
| Recommended PCB hole size | ϕ 1.5mm |

| TYPE NO. | POLES | LENGTH |
|-------------|-------|--------|
| CTBPTDVG/2 | 6 | 12.5mm |
| CTBPTDVG/3 | 9 | 17.5mm |
| CTBPTDVG/4 | 12 | 22.5mm |
| CTBPTDVG/5 | 15 | 27.5mm |
| CTBPTDVG/6 | 18 | 32.5mm |
| CTBPTDVG/7 | 21 | 37.5mm |
| CTBPTDVG/8 | 24 | 42.5mm |
| CTBPTDVG/9 | 27 | 47.5mm |
| CTBPTDVG/10 | 30 | 52.5mm |
| CTBPTDVG/11 | 33 | 57.5mm |
| CTBPTDVG/12 | 36 | 62.5mm |

