

No.	Murata Global P/N	Size (EIA)	TC Code	Rated Voltage	Cap.	Tol.	QTY
1	GJM1555C1HR10WB01	0402	COG	50Vdc	0.1pF	±0.05pF	20
2	GJM1555C1HR20WB01	0402	COG	50Vdc	0.2pF	±0.05pF	20
3	GJM1555C1HR30WB01	0402	COG	50Vdc	0.3pF	±0.05pF	20
4	GJM1555C1HR40WB01	0402	COG	50Vdc	0.4pF	±0.05pF	20
5	GJM1555C1HR50WB01	0402	COG	50Vdc	0.5pF	±0.05pF	20
6	GJM1555C1HR60WB01	0402	COG	50Vdc	0.6pF	±0.05pF	20
7	GJM1555C1HR70WB01	0402	COG	50Vdc	0.7pF	±0.05pF	20
8	GJM1555C1HR80WB01	0402	COG	50Vdc	0.8pF	±0.05pF	20
9	GJM1555C1HR90WB01	0402	COG	50Vdc	0.9pF	±0.05pF	20
10	GJM1555C1H1R0BB01	0402	COG	50Vdc	1.0pF	±0.1pF	20
11	GJM1555C1H1R1BB01	0402	COG	50Vdc	1.1pF	±0.1pF	20
12	GJM1555C1H1R2BB01	0402	COG	50Vdc	1.2pF	±0.1pF	20
13	GJM1555C1H1R3BB01	0402	COG	50Vdc	1.3pF	±0.1pF	20
14	GJM1555C1H1R5BB01	0402	COG	50Vdc	1.5pF	±0.1pF	20
15	GJM1555C1H1R6BB01	0402	COG	50Vdc	1.6pF	±0.1pF	20
16	GJM1555C1H1R8BB01	0402	COG	50Vdc	1.8pF	±0.1pF	20
17	GJM1555C1H2R0BB01	0402	COG	50Vdc	2.0pF	±0.1pF	20
18	GJM1555C1H2R2BB01	0402	COG	50Vdc	2.2pF	±0.1pF	20
19	GJM1555C1H2R4BB01	0402	COG	50Vdc	2.4pF	±0.1pF	20
20	GJM1555C1H2R7BB01	0402	COG	50Vdc	2.7pF	±0.1pF	20
21	GJM1555C1H3R0BB01	0402	COG	50Vdc	3.0pF	±0.1pF	20
22	GJM1555C1H3R3BB01	0402	COG	50Vdc	3.3pF	±0.1pF	20
23	GJM1555C1H3R6BB01	0402	COG	50Vdc	3.6pF	±0.1pF	20
24	GJM1555C1H3R9BB01	0402	COG	50Vdc	3.9pF	±0.1pF	20
25	GJM1555C1H4R0BB01	0402	COG	50Vdc	4.0pF	±0.1pF	20
26	GJM1555C1H4R3BB01	0402	COG	50Vdc	4.3pF	±0.1pF	20
27	GJM1555C1H4R7BB01	0402	COG	50Vdc	4.7pF	±0.1pF	20
28	GJM1555C1H5R0BB01	0402	COG	50Vdc	5.0pF	±0.1pF	20
29	GJM1555C1H5R1CB01	0402	COG	50Vdc	5.1pF	±0.25pF	20
30	GJM1555C1H5R6CB01	0402	COG	50Vdc	5.6pF	±0.25pF	20
31	GJM1555C1H6R0CB01	0402	COG	50Vdc	6.0pF	±0.25pF	20
32	GJM1555C1H6R2CB01	0402	COG	50Vdc	6.2pF	±0.25pF	20
33	GJM1555C1H6R8CB01	0402	COG	50Vdc	6.8pF	±0.25pF	20
34	GJM1555C1H7R0CB01	0402	COG	50Vdc	7.0pF	±0.25pF	20
35	GJM1555C1H7R5CB01	0402	COG	50Vdc	7.5pF	±0.25pF	20
36	GJM1555C1H8R0CB01	0402	COG	50Vdc	8.0pF	±0.25pF	20
37	GJM1555C1H8R2CB01	0402	COG	50Vdc	8.2pF	±0.25pF	20
38	GJM1555C1H9R0CB01	0402	COG	50Vdc	9.0pF	±0.25pF	20
39	GJM1555C1H9R1CB01	0402	COG	50Vdc	9.1pF	±0.25pF	20
40	GJM1555C1H100GB01	0402	COG	50Vdc	10pF	±2%	20
41	GJM1555C1H120GB01	0402	COG	50Vdc	12pF	±2%	20
42	GJM1555C1H150GB01	0402	COG	50Vdc	15pF	±2%	20
43	GJM1555C1H180GB01	0402	COG	50Vdc	18pF	±2%	20
44	GJM1555C1H200GB01	0402	COG	50Vdc	20pF	±2%	20
45	GJM1555C1H220GB01	0402	COG	50Vdc	22pF	±2%	20
46	GJM1555C1H270GB01	0402	COG	50Vdc	27pF	±2%	20
47	GJM1555C1H330GB01	0402	COG	50Vdc	33pF	±2%	20
48	GJM1555C1H390GB01	0402	COG	50Vdc	39pF	±2%	20
49	GJM1555C1H470GB01	0402	COG	50Vdc	47pF	±2%	20