

No.	Murata Global P/N	Size (EIA)	TC Code	Rated Voltage	Cap.	Tol.	QTY
1	GRM1555C1H1R0CA01	0402	COG	50Vdc	1.0pF	±0.25pF	100
2	GRM1555C1H1R2CA01	0402	COG	50Vdc	1.2pF	±0.25pF	20
3	GRM1555C1H1R5CA01	0402	COG	50Vdc	1.5pF	±0.25pF	20
4	GRM1555C1H1R8CA01	0402	COG	50Vdc	1.8pF	±0.25pF	20
5	GRM1555C1H2R2CA01	0402	COG	50Vdc	2.2pF	±0.25pF	20
6	GRM1555C1H2R7CA01	0402	COG	50Vdc	2.7pF	±0.25pF	20
7	GRM1555C1H3R3CA01	0402	COG	50Vdc	3.3pF	±0.25pF	20
8	GRM1555C1H3R9CA01	0402	COG	50Vdc	3.9pF	±0.25pF	20
9	GRM1555C1H4R7CA01	0402	COG	50Vdc	4.7pF	±0.25pF	20
10	GRM1555C1H5R6CA01	0402	COG	50Vdc	5.6pF	±0.25pF	20
11	GRM1555C1H6R8CA01	0402	COG	50Vdc	6.8pF	±0.25pF	20
12	GRM1555C1H8R2CA01	0402	COG	50Vdc	8.2pF	±0.25pF	20
13	GRM1555C1H100JA01	0402	COG	50Vdc	10pF	±5%	100
14	GRM1555C1H150JA01	0402	COG	50Vdc	15pF	±5%	20
15	GRM1555C1H220JA01	0402	COG	50Vdc	22pF	±5%	20
16	GRM1555C1H330JA01	0402	COG	50Vdc	33pF	±5%	20
17	GRM1555C1H470JA01	0402	COG	50Vdc	47pF	±5%	20
18	GRM1555C1H680JA01	0402	COG	50Vdc	68pF	±5%	20
19	GRM1555C1H101JA01	0402	COG	50Vdc	100pF	±5%	100
20	GRM1555C1H151JA01	0402	COG	50Vdc	150pF	±5%	20
21	GRM1555C1H221JA01	0402	COG	50Vdc	220pF	±5%	20
22	GRM1555C1H331JA01	0402	COG	50Vdc	330pF	±5%	20
23	GRM1555C1H471JA01	0402	COG	50Vdc	470pF	±5%	20
24	GRM1555C1H681JA01	0402	COG	50Vdc	680pF	±5%	20
25	GRM1555C1H102JA01	0402	COG	50Vdc	1000pF	±5%	100
26	GRM155R71H102KA01	0402	X7R	50Vdc	1000pF	±10%	100
27	GRM155R71H152KA01	0402	X7R	50Vdc	1500pF	±10%	20
28	GRM155R71H222KA01	0402	X7R	50Vdc	2200pF	±10%	20
29	GRM155R71H332KA01	0402	X7R	50Vdc	3300pF	±10%	20
30	GRM155R71H472KA01	0402	X7R	50Vdc	4700pF	±10%	20
31	GRM155R71H682KA88	0402	X7R	50Vdc	6800pF	±10%	20
32	GRM155R71H103KA88	0402	X7R	50Vdc	0.01μF	±10%	100
33	GRM155R71H153KA12	0402	X7R	50Vdc	0.015μF	±10%	20
34	GRM155R71H223KA12	0402	X7R	50Vdc	0.022μF	±10%	20
35	GRM155R71H333KE14	0402	X7R	50Vdc	0.033μF	±10%	20
36	GRM155R71H473KE14	0402	X7R	50Vdc	0.047μF	±10%	20
37	GRM155R71H683KE14	0402	X7R	50Vdc	0.068μF	±10%	20
38	GRM155R71H104KE14	0402	X7R	50Vdc	0.1μF	±10%	100
39	GRM155R71C224KA12	0402	X7R	16Vdc	0.22μF	±10%	20
40	GRM155R6YA224KE01	0402	X5R	35Vdc	0.22μF	±10%	20
41	GRM155R71A474KE01	0402	X7R	10Vdc	0.47μF	±10%	20
42	GRM155R6YA474KE01	0402	X5R	35Vdc	0.47μF	±10%	20
43	GRM155R6YA105KE11	0402	X5R	35Vdc	1μF	±10%	100
44	GRM155R70J105KA12	0402	X7R	6.3Vdc	1μF	±10%	100
45	GRM155R61E225KE11	0402	X5R	25Vdc	2.2μF	±10%	20
46	GRM155R61A475MEAA	0402	X5R	10Vdc	4.7μF	±20%	20
47	GRM155R60J106ME15	0402	X5R	6.3Vdc	10μF	±20%	100