




OYN-X | 4-IN-1 VARIFOCAL P400

1080P FULL HD DIGITAL CAMERA • AHD • TVI • CVI • 960H

KEY FEATURES

- 1080P/2.4MP
- Day & Night
- Sens-Up
- 3DNR Noise Reduction
- IP66 Rating
- IR Cut Filter
- OSD Menu
- 12V DC
- Wide Dynamic Range (WDR)
- Armoured Housing



SPECIFICATION	4X-P400-VFG
CAMERA	
Image Sensor	1/2.7" 1080P Full HD Digital Image Sensor
Signal System	PAL / NTSC
Active Pixels	1928(H) x 1088(V)
Lens	2.8-12mm MP Lens
Angle of View	H: 98° - 32°
Horizontal Resolution	1080P
S/N Ratio	>50 dB (AGC OFF)
Min Illumination	0 Lux (IR ON - IR-cut Technology)
Menu	UTC Control
Language	ENGLISH / CHINESE / ITALIAN / SPANISH
Auto Electronic Shutter	PAL: 1/50 - 1/100,000 Sec NTSC: 1/60 - 1/100,000 Sec
DNR	0-15
D-WDR	ON / OFF
Auto Gain Control	Built-in
Video Output	AHD / TVI / CVI / CVBS (Factory default is AHD)
Power Supply	DC12V±10%
Current Consumption	70 mA (IR OFF), 390 mA (IR ON)
IR Led	48 Pcs
IR Distance in Effect	40-50M
IP Rating	IP66
Storage Temperature	-50°C ~ +90°C
Operating Temperature	-30°C ~ +70°C
Dimension	240mm x 105mm x 200mm
Weight	1210g

SPECIFICATION

- Sensor: Sony 2.4MP 1/2.7" 2.4MP
- DSP: Nextchip-2441H
- Up to 50M IR Range
- 48 Pcs IR Leds
- Dimensions: 240mm x 105mm x 200mm
- Lens: 2.8-12mm Varifocal