

WTHA1 Hot Air Station

Featuring a built-in, high performance hot air pencil

900 W power, compact, easy-operating station with a smart temperature profile mode adjustable for diverse rework applications, assuring fast, safe performance. Up to 100 l / min expanded hot air.



Product picture similar



Features and Benefits

- > Front panel power switch
- > Multi-function LCD screen
- > Quick access menu button
- > Stackable unit
- > 5 Pre-sets / temperature profile
- > Up to 5 pre-sets available
- > Finger-activated switch on hot air pencil
- > Flexible silicone hose

Technical Data

Dimensions L x W x H	210 x 160 x 125 mm 8.30 x 6.30 x 4.90 in
Fuse 120 V (A)	T8 A
Weight	3.0 kg / 6.6 lbs
Power supply	120 V / 60 Hz
Power consumption	900 W
ESD safe	Yes
Temperature range (expanded hot air) l/min 100	50 °C – 600 °C 120 °F – 1100 °F
Temperature accuracy	± 30 °C / ± 54 °F

Order no.	Part description	List USD	List CAN
WTHA1 Hot Air Station			
WTHA1N	WTHA1 HOT AIR STATION, 900 W	\$650.00	\$819.00

Nozzles			
T0058768742	TNR 25 ROUND NOZZLE 2.5MM FOR WTHA	\$49.99	\$62.99
T0058768743	TNR 40 ROUND NOZZLE 4MM FOR WTHA	\$13.61	\$17.15
T0058768744	TNR 70 ROUND NOZZLE 7MM FOR WTHA	\$24.14	\$30.42
T0058768745	TNRB 17 ROUND NOZZLE 1.7MM X 45° FOR WTHA	\$52.03	\$65.56
T0058768746	TNRB 60 ROUND NOZZLE 6MM X 45° FOR WTHA	\$40.69	\$51.27
T0058768747	TNA NOZZLE ADAPTER FOR WTHA	\$31.16	\$39.26

Accessories			
T0058768762	SILICON PAD FOR WTHA1 PACKED	\$21.50	\$27.09
T0058757898	HOLDER RECLINED FOR HAP 3	\$60.15	\$75.79