

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0008560108**
Status: **Active**
Overview: KK® Interconnect System - Molex
Description: KK® 396 Crimp Terminal 2578, 22-26 AWG, Bag, Brass, 0.51µm Selective Gold (Au)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-2759-001 \(PDF\)](#)

General

Product Family Crimp Terminals
 Series 2578
 Application Power
 Crimp Quality Equipment Yes
 Overview KK® Interconnect System - Molex
 Packaging Alternative 08-56-0107 (Reel)
 Product Name KK® 396, KK® 508
 UPC 800753745933

Physical

Gender Female
 Material - Metal Brass
 Material - Plating Mating Gold
 Material - Plating Termination Gold
 Net Weight 0.150/g
 Packaging Type Bag
 Plating min - Mating 0.381µm
 Plating min - Termination 0.051µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 1.65mm max.
 Wire Size AWG 22, 24, 26
 Wire Size mm² N/A

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number 2578-(550)L

Reference - Drawing Numbers

Packaging Specification PK-2759-001
 Sales Drawing SD-2578



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/21/2016 (20 June
 2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS
 ELV

Green Image
 Not Relevant

Search Parts in this Series

2578 Series

Use With

2574 , 2139 , 41695 , 3069 , 6422 , 5265 ,
5239

Application Tooling | FAQ

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

Description	Product #
Extraction Tool	<u>0011030016</u>
Hand Crimp Tool for Crimp Terminals	<u>0638117400</u>

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION