

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191990008](#)
Status: **Active**
Overview: [Splices](#)
Description: Avikrimp™ Window Butt Connector for 18-22 AWG Wire, Mylar Tape Carrier

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Splices
Series	19199
Comments	Mil Spec M7928/5-3
Crimp Quality Equipment	Yes
Mil-Spec	M7928/5-3
Overview	Splices
Product Name	Avikrimp™, Butt - Window
UPC	800753046818

Physical

Barrel Type	Closed
Color - Resin	Red
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.194/g
Packaging Type	Adhesive Tape on Reel
Temperature Range - Operating	-55°C to +105°C
Wire Insulation Diameter	3.56mm max.
Wire Size AWG	18, 20, 22
Wire Size mm²	0.25-1.50

Electrical

Voltage - Maximum	300V
-------------------	------

Material Info

Old Part Number	WA-840T
-----------------	---------

Reference - Drawing Numbers

Sales Drawing	SD-19199-003
---------------	--------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

Search Parts in this Series

[19199 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	0192880043
Mini-Mac™ Applicator Air Feed-Mylar Tape	0638859100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION