

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192160005](#)
Status: **Active**
Overview: [Splices](#)
Description: Multi-Lock Connector for 18-22 AWG Wire

Documents:

3D Model	Product Specification PS-19902-013 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19902-011 (PDF)	

Agency Certification

UL E32244

General

Product Family	Splices
Series	19216
Comments	13.97 x 9.53mm when closed
Crimp Quality Equipment	Yes
Mil-Spec	N/A
MolexKits	Yes
Overview	Splices
Product Name	Multi-Lock
UPC	800753025936

Physical

Barrel Type	Closed
Color - Resin	Red
Flammability	94V-0
Insulation	Polypropylene
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.353/g
Packaging Type	Bag
Temperature Range - Operating	105°C
Wire Insulation Diameter	3.30mm & 4.06mm
Wire Size AWG	18, 20, 22
Wire Size mm ²	N/A

Electrical

Voltage - Maximum 600V

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Engineering Number ML-2218

Reference - Drawing Numbers

Product Specification	PS-19902-011, PS-19902-013
Sales Drawing	SD-19216-003



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/21/2016 (20 June 2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

China RoHS

Green Image

Not Relevant

Search Parts in this Series

[19216 Series](#)