

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0934442102](#)  
**Status:** **Active**  
**Overview:** ML-XT™ Sealed Connection System  
**Description:** ML-XT™ Sealed 3 Circuit Receptacle Housing, Pre-Assembled with Small Rear Seal and Cover, Grey

**Documents:**

[Drawing \(PDF\)](#) [Packaging Specification 934430002 \(PDF\)](#)  
[Product Specification 934430010 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Application Specification 934430010 \(PDF\)](#)

**General**

|                |  |
|----------------|--|
| Product Family | Crimp Housings                         |
| Series         | 93444                                  |
| Application    | Power, Signal, Wire-to-Wire            |
| Overview       | <u>ML-XT™ Sealed Connection System</u> |
| Product Name   | ML-XT™                                 |
| UPC            | 889056191425                           |

**Physical**

|                               |                 |
|-------------------------------|-----------------|
| Circuits (maximum)            | 3               |
| Color - Resin                 | Grey            |
| Gender                        | Receptacle      |
| Glow-Wire Compliant           | No              |
| Keying to Mating Part         | None            |
| Lock to Mating Part           | Yes             |
| Material - Resin              | Nylon           |
| Net Weight                    | 6.892/g         |
| Number of Rows                | 2               |
| Packaging Type                | Bag             |
| Panel Mount                   | No              |
| Pitch - Mating Interface      | N/A             |
| Polarized to Mating Part      | Yes             |
| Temperature Range - Operating | -55°C to +125°C |

**Electrical**

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 13.0A |
|-------------------------------|-------|

**Material Info**

**Reference - Drawing Numbers**

|                           |           |
|---------------------------|-----------|
| Application Specification | 934430010 |
| Packaging Specification   | 934430002 |
| Product Specification     | 934430010 |
| Sales Drawing             | 934430020 |



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
ELV

Green Image  
Not Relevant

**Search Parts in this Series**

[93444 Series](#)

**Mates With**

ML-XT™ Sealed 3 Circuit Plug Housing  
[93445-2102](#)

**Use With**

ML-XT™ Male (Pin) Terminal [84524-0004](#) (Nickel), ML-XT™ Male (Pin) Terminal [84524-0014](#) (Selective Gold), ML-XT™ 3 Circuit Receptacle Wedgelock [93447](#) , ML-XT™ Blind Cavity Plug [93494-1000](#)