

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0934452101](#)  
**Status:** **Active**  
**Overview:** [ML-XT™ Sealed Connection System](#)  
**Description:** ML-XT™ Sealed 3 Circuit Plug Housing, Pre-Assembled with Small Rear Seal and Cover, Black

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Crimp Housings
Series	<a href="#">93445</a>
Application	Power, Signal, Wire-to-Wire
Application Tooling Part Link	<a href="#">63824-5300</a>
Overview	<a href="#">ML-XT™ Sealed Connection System</a>
Product Name	ML-XT™
UPC	889056189972

**Physical**

Circuits (maximum)	3
Color - Resin	Black
Gender	Plug
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	6.070/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55°C to +125°C

**Electrical**

Current - Maximum per Contact	13.0A
-------------------------------	-------

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	934430020
---------------	-----------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Reviewed

**Search Parts in this Series**

[93445](#) Series

**Mates With**

ML-XT™ Sealed 3 Circuit Receptacle Housing [93444-2101](#)

**Use With**

ML-XT™ Female (Socket) Terminal [84525-0009](#) (Nickel), ML-XT™ Female (Socket) Terminal [84525-0032](#) (Selective Gold), ML-XT™ 3 Circuit Plug Wedgelock [93448](#) , ML-XT™ Blind Cavity Plug [93494-1000](#)