

happening now. . .

Energizer® headlight transition

ensure transition



Replacement




	Obsolete	Replacement
Energizer Type Name	HDL33AINE	HDBIN32E
Light Output	95 lumens	150 lumens
Runtime	8.5 hours	8 hours
Beam Distance	18 meters	40 meters
Water Resistance	IPX4	IPX4
Features	White Spot, White Flood, White Spot/Flood, Red for night vision, Strobe Feature, Pencil holders	White Spot, White Flood, White Spot/Flood. Dimmable to control brightness and runtime

ensure transition



Replacement



	Obsolete	Replacement
Energizer Type Name	INHD5L32E	HDDIN32E
Light Output	130 lumens	250 lumens
Runtime	5.5 hours	6 hours
Beam Distance	70 meters	80 meters
Water Resistance	IPX4	IPX4
Features	White Spot, White Flood, White Spot/Flood, Green for inspection, Pencil holders	White Spot, White Flood, Red for night vision. Digital light focus and memory recall

© 2015 Energizer Energizer, Energizer Bunny design and certain graphic designs are trademarks of Energizer Brands, LLC and related subsidiaries

TM

that's positivenergy 


happening now. . .

Energizer® headlight transition

ensure transition



Replacement




	Obsolete	Replacement
Energizer Type Name	HD33A1EN	HDA32E
Light Output	50 lumens	80 lumens
Runtime	12 hours	7 hours
Beam Distance	27 meters	30 meters
Water Resistance	IPX4	IPX4
Features	White High mode, White Low mode	White High mode, White Low mode

ensure transition



Replacement



	Obsolete	Replacement
Energizer Type Name	HD7L33AE	HDC32E
Light Output	115 lumens	200 lumens
Runtime	5.5 hours	6 hours
Beam Distance	25 meters	70 meters
Water Resistance	IPX4	IPX4
Features	White Spot, White Flood, White Spot/Flood, Red for night vision	White Spot, White Flood, White Spot/Flood, Red for night vision. Dimmable to control brightness and runtime

© 2015 Energizer Energizer, Energizer Bunny design and certain graphic designs are trademarks of Energizer Brands, LLC and related subsidiaries

TM

that's positivenergy 