

Category 6 Keystone Panel Mount Coupler (Shielded)



Category 6 Keystone Panel Mount Coupler Shielded (SACK3S, SACK3S-24)

Features

- Designed to fit US industry standard keystone mount outlets wall plates and patch panels
- RJ45 complies with FCC68
- High performance data throughput, meets Category 6 data transfer rates
- Operating temperature: ~40°C ~ +60°C
- Jack insertion life > 750 mating cycles
- Available as part of our innovative Panel Mount and D UNIVERSAL ranges

Packaging:

- Standard product is supplied in individual polythene bags. To save time for panel assemblers, SACK3S-24 is available as a “bulk pack” of 24 pieces without individual bags.

Specifications

- **Materials:**
Housing: Nickel plated zinc alloy
Contacts: 50µ"/ 1.27µm gold plating over nickel plated phosphor bronze
Earthing lug material: Stainless steel SUS304
- **Weight:**
SACK3S: 18g approx. SACK3S-24: 460g approx.
- **Dimensions**
SACK3S: 29.7 x 17 x 16.1 mm approx. SACK3S-24: 280 x 70 x 35mm approx.

ROHS Compliant







DATE	2014/08/14
Revision	A

Features :

- RJ45 complies with FCC part 68 standard
- Jack Insertion life >750 mating cycles
- Operating temperature : -40°C~+60°C

Electrical :

- Contact resistance : 20m ohm
- DC Current rating : 1,5Amps
- DC resistance : Max.0.1 ohm
- Insulation Resistance : 500m ohm
- Dielectric withstanding voltage : 1000V
- * Earthing lug material: Stainless steel SUS304



TOLERANCE	
.XXXX	—
.XXX	0.10
.XX	0.25
.X	0.38

MATERIAL	
CATEGORY	<input type="checkbox"/> CAT.5E <input checked="" type="checkbox"/> CAT.6 <input type="checkbox"/> CAT.3 <input type="checkbox"/> OTHER_____
HOUSING	Zn alloy
CONTACT	0.46 mm DIAMETER PHOSPHOR BRONZE GOLD PLATED OVER NICKEL
GOLD-PLATING	<input type="checkbox"/> 0,0762um/3u Inch <input type="checkbox"/> 0,15um/6u Inch <input type="checkbox"/> 0,38um/15u Inch <input type="checkbox"/> 0,76um/30u Inch <input checked="" type="checkbox"/> 1,27um/50u Inch
COLOR	<input type="checkbox"/> WHITE <input type="checkbox"/> BLACK <input type="checkbox"/> GREEN <input type="checkbox"/> BLUE <input type="checkbox"/> YELLOW <input type="checkbox"/> RED <input type="checkbox"/> ORANGE <input type="checkbox"/> IVORY <input type="checkbox"/> OTHER_____
Cosmetic	Electroplating Ni + Sandblasting

P/NO. SACK3S	
ITEM. Inline Coupler	CO. EX2136
DR. Wakka 2014/08/14	APPD.
TUK Ltd	
FILE. SACK3S	SCALE /
UNIT mm	SIZE A4

REV.	DESCRIPTION	ENG.	APPROVAL
1	2	3	4

1 2 3 4 5 6 7