

Basic

Aspect Ratio:	16:9
Backlight Technology:	LED
Brand Name:	Acer
Brightness:	200 cd/m ²
Colour Support:	16.7 Million Colours
Colour:	Black
Contrast Ratio:	100,000,000:1
Environmental Certification:	MPR II
Environmentally Friendly:	Yes
Maximum Resolution:	1366 x 768
Number of Screens:	1
Product Family:	V
Product Type:	LCD Monitor
Response Time:	5 ms
Screen Mode:	HD
Screen Size:	49.5 cm (19.5")
VGA:	Yes

Camera

Screen Size:	49.5 cm (19.5")
--------------	-----------------

Display & Graphics

Aspect Ratio:	16:9
Backlight Technology:	LED
Brightness:	200 cd/m ²
Colour Support:	16.7 Million Colours
Contrast Ratio:	100,000,000:1
Maximum Resolution:	1366 x 768
Response Time:	5 ms
Screen Mode:	HD
Screen Size:	49.5 cm (19.5")

Energy & Performance

Maximum Resolution:	1366 x 768
Off-Mode Power Consumption:	170 mW
Standby Power Consumption:	350 mW

General Information

Brand Name:	Acer
Manufacturer Part Number:	UM.IV6EE.B01
Manufacturer Website Address:	http://www.acer.co.uk
Manufacturer:	Acer, Inc
Package Contents:	

- V206HQL Widescreen LCD Monitor
- Power Cord
- 1 x VGA Cable

Product Model:	V206HQL
Product Name:	V206HQL Widescreen LCD Monitor
Product Series:	V
Product Type:	LCD Monitor

Image

Aspect Ratio:	16:9
Brightness:	200 cd/m ²
Colour Support:	16.7 Million Colours
Contrast Ratio:	100,000,000:1
Maximum Resolution:	1366 x 768

Interfaces/Ports

VGA:	Yes
------	-----

Miscellaneous

Environmental Certification:	MPR II
Environmentally Friendly:	Yes
Package Contents:	

- V206HQL Widescreen LCD Monitor
- Power Cord
- 1 x VGA Cable

Physical Characteristics

Colour:	Black
Depth with Stand:	191 mm

Depth:	50 mm
Height with Stand:	362.20 mm
Height:	276.2 mm
Weight (Approximate):	2.50 kg
Weight with Stand (Approximate):	2.90 kg
Width with Stand:	463.40 mm
Width:	463.4 mm

Power Description

Off-Mode Power Consumption:	170 mW
Operating Power Consumption (Energy Star):	11 W
Standby Power Consumption:	350 mW

Product Information

Brightness:	200 cd/m ²
Colour Support:	16.7 Million Colours
Maximum Adjustable Height:	No
Screen Size:	49.5 cm (19.5")
Width:	463.4 mm

Technical Information

Aspect Ratio:	16:9
Backlight Technology:	LED
Brightness:	200 cd/m ²
Contrast Ratio:	100,000,000:1
Maximum Adjustable Height:	No
Maximum Resolution:	1366 x 768
Number of Screens:	1
Panel Technology:	Twisted Nematic Film (TN Film)
Response Time:	5 ms
Screen Mode:	HD
Screen Size:	49.5 cm (19.5")
Swivel Angle:	No
Tilt Angle:	-5°to25°

Video

Aspect Ratio:	16:9
Brightness:	200 cd/m ²
Colour Support:	16.7 Million Colours
Contrast Ratio:	100,000,000:1
Maximum Resolution:	1366 x 768
Screen Mode:	HD

Warranty

Limited Warranty:	3 Year
-------------------	--------