




Product information MAS 30 grau/grey

Industrial Connecting Solutions: Circular Connectors: Audio/Video Connectors: DIN EN 60 130-09 Connectors (MAS/MAK series): without locking screw: Straight plugs: MAS 30 grau/grey

<https://e-catalog.hirschmann.com:443/link/57078-24228-256281-256282-24384-24385-24387-34376/en/conf/ulistate>

Name	MAS 30 grau/grey
	
	plug with insulated handle; solder joint
Delivery informations	
Availability	available
Product description	
Type	MAS 30 grau/grey
Order No.	930 014-517
Type of contact	male
Description	plug with insulated handle; solder joint
Housing Color	grey
Number of contacts	3
Conductor size	$\leq 0.34 \text{ mm}^2$
Technical data	
LF output "Phone"	EN 60 130-09
Pole arrangement DIN	DIN 41524
Rated current	4 A
Rated voltage	AC/DC 34 V
Cable diameter	5.5 mm
Type of termination	solder
Material	
Contact material	brass
Contact surface material	tin plated
Contact bearer material	PA 66/UL standard 94V-2
Housing material	PE
Environmental conditions	
Protection class (IEC 60529)	IP 30
Temperature range	-20 °C to +60 °C
Scope of delivery and accessories	
Packaging	retail package, polyethylene bag

