

# MASK4-W

4.25" small design two-way  
loudspeaker , white



The MASK4 low impedance loudspeaker has a unique and innovative design which supplies you with a crystal clear sound, from back ground music up to “dance level” music. The cabinet is made of high quality enforced PP4 ABS.

The grille is made of aluminium and the woofer has been coated so MASK4 loudspeakers are suitable for both indoor and outdoor use. The cabinet is supplied with a rubber IP protection cover for the loudspeaker terminals. This way water ingress and corrosion of the terminals is avoided.

The built-in Auto-Reset 3-step Protection Guard together with the quality components makes MASK4 a fail-safe loudspeaker, even at high power loads! MASK4 has a powerful 4.25” coated paper cone woofer. Together with the Vari-throat horn for the Ferro-fluid cooled 1” silk dome tweeter this results in a high SPL and ultra low distortion.

Its phase alignment and wide frequency range makes sure every note, starting from the robust low-mid over the clean middle range to the crystal clear highs, reaches your ears with an astonishing clarity.

Thanks to the Intelli-Mount bracket, the MASK4 is easy and fast to install. The Vari-throat horn for the tweeter and the 5° down tilt angle in which the woofer and tweeter are mounted in the cabinet, guarantee a perfect sound dispersion, without the need of a big tilt angle of the cabinet itself. The cabinet has a M8 thread mounting point tapped at the back of the cabinet. This way many other mounting systems can be used.

From 12 pieces on, MASK4 loudspeakers can be painted in any other RAL colour.

## TECHNICAL SPECIFICATIONS

height in mm	220	width in mm	129
depth in mm	130	loudspeaker system	2-way
woofer size in inch	4,25	woofer cone material	coated paper
tweeter size in inch	1	mounting system	intellimount
colour	black / white / silver	impedance (ohms)	8
low impedance dynamic power in watts	70	SPL 1W/1m in dB	92
max SPL 1m in dB	104	frequency response in Hz	80 - 20K
main construction material	ABS plastic	grille main material	aluminium
IP rating	64	Horizontal dispersion angle 1000 Hz	180°
Vertical dispersion angle 1000 Hz	180°	Net weight product (kg)	1,85

[MORE PICTURES](#)



ACCESSORIES



**MASKW-W**

Double V-shaped cluster bracket for MASK4(T)-W/MASK6(T)-W



**MASKV-W**

V-shaped 2-way cluster bracket for MASK4(T)-W / MASK6(T)-W



**MASKL-W**

L-shaped side bracket for MASK4(T)-W / MASK6(T)-W