

ERA Garrison - Smartphone GSM/SMS Kit (E2)



Features

- GSM/SMS Communicating Alarm with integrated Mobile Phone Technology
- Backlit Touch Control Keypad with GSM signal confirmation indicator
- Built-in SIM Card holder (accepts standard size SIM Card)
- Self-monitoring with SMS notifications for Alarm, Emergency and Tamper
- SMS text alerts for: arming/disarming, intruder, tamper, power failure and recovery
- Control Panel – automatic back-up battery low power alert
- Remote Monitoring with 'Listen-in' and 'Two-way' talk
- Arm, Part Arm, Disarm Modes (silent part arming)
- Adjustable Entry/Exit delay
- Event Log
- Sensor/zone naming – name up to 50 Sensors
- Pet Friendly PIR Motion Sensor
- Store 5 x Emergency phone numbers and 5 x SMS numbers
- Speed dial to master phone number - hands free calling
- 'Listen-in' and 'Two-way' talk
- Voice Memo - Record/play back
- Built-in Siren with adjustable volume and duration
- Supports up to 10 Remote Controls and 50 Wireless Sensors
- Pet Friendly
- All batteries included
- Tamper protection

Key Features

- Compact Control Panel with Touch keypad
- Remote monitoring and control from anywhere in the world with the free App and by SMS text
- Automatic alerts/notifications include: intrusion, emergency, disarm, power failure, flood, smoke
- Personalised SMS text notifications, i.e. 'Jack has disarmed the system'
- Remote 'Listen-in' and 'Two-way' talk
- Zone naming for easy identification of affected area, i.e. 'zone 1 Alarm: Entrance Door Sensor'
- Pet Friendly
- All batteries included

Search for the free
'ERA Garrison Alarm' App



ERA Garrison - Smartphone GSM/SMS Kit (E2)

Ordering Details

Product	Part No.
ERA Garrison	
Alarm kit	ERA-GARRISON
Additional Accessories	
Pet Friendly PIR Sensor	EPIR
Door/Window Sensor	EMAG
Remote Control	EREM
Wifi HD Camera	IP116
Ceiling Mounted PIR Sensor	P700
Narrow Beam PIR Sensor	P800
Vibration Sensor	WD80
Smoke Detector	SMK500
Water Detector	WI210
Personal Alert Button	SOS100
Range Extender	RT101
Indoor Plug-in Siren	WS105
Solar Charged Siren	ESS260B
Replica Siren	ERS26B
Outdoor Mains Powered Siren	WS280


Technical Information

Item	Parameter
Model No	E2
Control Panel's Power Supply	Input: AC 110-240V/50-60Hz Output : DC 12V/500mA
GSM Working Frequency	850/900/1800/1900MHz
Standby Current	≤56mA
Alarm Current	≤270mA
Transmitting Distance	≤80metres (in open field conditions)
Internal Battery Backup	Li-ion Battery: 3.7V/600mAh
Internal Siren	90dB
Supports up to	10pcs Remote Controls, 50pcs Wireless Accessories
Radio Frequency	433MHz
Housing Material	ABS Plastic
Operation Conditions	Temperature: -10°C - 55°C Humidity: ≤80% (non-condensing)
Dimensions (L x W x H)	Panel: 125mm x 150mm x 30mm Bracket: 87.5mm x 81.5mm x 12mm
EAN	5060215565034
Outer Carton Qty	20
Outer Carton Dimensions	500mm x 425mm x 290mm
Outer Carton Weight	18kg

Packaging

Kit Content
Control Panel (with back-up battery and internal siren) x 1, Adapter x 1, Pet Friendly PIR Motion Sensor x 1, Door/Window Sensor x 1, Remote Control x 2, all Batteries, all Fittings, Instruction Manual.

Suggested Installation Layout



ERA reserves the right to change specification without notice. It is the responsibility of the householder or installer to ensure that the finished product meets any required safety and performance specification.