

ERA Invincible - Dual Network Comms Kit (E11)



Features

- Dual Network GSM/GPRS, PSTN (landline)
- Selectable alert notification network preferences, i.e. landline and/or SMS text and/or GPRS message
- Remote monitoring: 'Listen-in' and 'Two-way' talk
- SMS text alerts for: arming/disarming, intruder, tamper, power failure/recovery, RFID Tag identification
- Built-in SIM Card holder (accepts standard size SIM Card)
- Quick disarm at the Control Panel by RFID Contactless Tag
- Nameable Tags for easy identification of 'who disarmed the system and when'
- Built-in siren with adjustable volume and duration
- Arm, Part Arm, Disarm Modes (silent part arming)
- Adjustable Entry/Exit delay
- Sensor/Zone naming – up to 50 Sensors
- Store 5 x Emergency phone numbers and 5 x SMS numbers
- Speed dial to master phone number - hands free calling
- Voice Memo - Record/playback
- 150 Event Log
- Supports up to 10 Remote Controls and 50 Wireless Sensors & 50 RFID Contactless Tags
- Pet Friendly
- All batteries included
- Tamper protection

Key Features

- Remote monitoring and control from anywhere in the world with the free App and by SMS text
- Automatic alerts/notifications include: intrusion, emergency, disarm, power failure/recovery, flood, smoke
- Backlit LCD Screen Control Panel with Touch keypad and RFID reader
- Personalised SMS text notifications, i.e. 'Jack has disarmed the system'
- RFID Contactless Tags can be named for Tag user identification
- Zone naming for easy identification of affected area, i.e. 'zone 1 Alarm: Entrance Door Sensor'
- Pet Friendly
- All batteries included

Search for the free
'ERA Invincible Alarm' App



ERA Invincible - Dual Network Comms Kit (E11)

Ordering Details

Product	Part No.
ERA Invincible	
Alarm kit	ERA-INVINCIBLE
Additional Accessories	
Pet Friendly PIR Sensor	EPIR
Door/Window Sensor	EMAG
Remote Control	EREM
Wifi HD Camera	IP116
Ceiling Mounted PIR Sensor	P700
Narrow Beam PIR Sensor	P800
Vibration Sensor	WD80
Smoke Detector	SMK500
Water Detector	WI210
RFID Keypad	KP700
RFID Contactless Tag	TAG26
Personal Alert Button	SOS100
Range Extender	RT101
Indoor Plug-in Siren	WS105
Solar Charged Siren	ESS260B
Replica Siren	ERS26B
Outdoor Mains Powered Siren	WS280


Technical Information

Item	Parameter
ERA Invincible	
Model No	E11
Control Panel's Power Supply	Input: AC 110-240V/50-60Hz Output : DC 12V/500mA, 6Wh
Standby Current	≤ 90mA
Alarm Current	≤ 300mA
Transmitting Distance	≤80metres (in open field condition)
Internal Battery Backup	3.7V/800mAh x 2pcs (BL-5B)
Battery Standby time	10 hours
Internal Siren	95dB
Allowed amount of expandable wireless accessories	10 pcs Remote Controls, 50pcs Wireless Accessories, and 50pcs RFID Contactless Tags
Maximum Event Logs	150 Events
Radio Frequency	433MHz
Housing Material	ABS Plastic
Screen	LCD Screen
Operation Condition	Temperature: -10°C - 55°C Humidity: ≤80% (non-condensing)
Dimensions (L x W x H)	Panel: 185mm x 130mm x 27mm LCD Screen: 61.70mm x 14.12mm
EAN	5060215565010
Outer Carton Qty	20
Outer Carton Dimensions	460mm x 415mm x 315mm
Outer Carton Weight	18.6Kgs

Packaging

Kit Content
Includes: Control Panel (with back-up battery and internal siren), Adapter x 1, Pet Friendly PIR Motion Sensor x 1, Door/Window Sensor x 1, Remote Control x 2, RFID Contactless Tags x 2, all Batteries, all Fittings, Instruction Manual.

Suggested Installation Layout



ERA reserves the right to change specification without notice. It is the responsibility of the householder or installer to ensure that the finished product meets any required safety and performance specification.