

AURELIA® Delight Lite®

Examination Gloves



-	(XS)	ø 100	10 x 100
32226	(S)	ø 100	10 x 100
32227	(M)	ø 100	10 x 100
32228	(L)	ø 100	10 x 100
32229	(XL)	ø 100	10 x 100



Vinyl



Powder Free



Clear



4.0 +/- 0.2 g



Smooth




3 Years

The gloves are made from a very soft, thin vinyl which allows for good, tactile sensitivity for all applications.

Beaded cuff, Ambidextrous, Glueless, Free of Thiurams
Straight fingers, Non-Sterile

Sizes & Dimensions



XS	75 ± 10 mm	min. 240 mm
S	80 ± 10 mm	min. 240 mm
M	95 ± 10 mm	min. 240 mm
L	110 ± 10 mm	min. 240 mm
XL	≥ 110 mm	min. 240 mm

Single wall thickness



- ① min. 0,06 mm
- ② min. 0,06 mm
- ③ min. 0,05 mm

Physical properties

	Unaged	Aged
Tensile Strength	min. 11,0 MPa	min. 11,0 MPa
Elongation	min. 350 %	min. 300 %
Strength at Break	min. 3,6 N	min. 3,6 N

Quality Signs & Certificates

89/686/EEC

ISO 9001:2008, ISO 13485, CMDCAS 13485 (SGS)

AQL1.5

EN 420:2003 + A 1:2009

EN 1186: Food Contact Approved (SGS)

