
Brand Name: HP
DisplayPort: Yes
Environmentally Friendly: Yes
Form Factor: Small Form Factor
Graphics Controller: Intel
Manufacturer:
Graphics Controller Model: HD Graphics 530
Graphics Memory Accessibility: Shared
Graphics Memory Technology: DDR4 SDRAM
Green Compliant: Yes
Number of USB 2.0 Ports: 4
Number of USB 3.0 Ports: 4
Operating System Architecture: 64-bit
Operating System Platform: Windows
Operating System: Windows 7 Professional
Optical Drive Type: DVD-Writer
Processor Manufacturer: Intel
Processor Model: i3-6100
Processor Speed: 3.70 GHz
Processor Type: Core i3
Product Family: Business Desktop ProDesk 400 G
Product Type: Desktop Computer
Standard Memory: 4 GB
Total Hard Drive Capacity: 500 GB
Total Number of USB Ports: 8
VGA: Yes

Display & Graphics

Graphics Controller: Intel
Manufacturer:
Graphics Controller Model: HD Graphics 530
Graphics Memory Accessibility: Shared
Graphics Memory Technology: DDR4 SDRAM

General Information

Brand Name: HP
Manufacturer Part Number: T4R69ET#ABU
Manufacturer Website Address: <http://www.hp.com>
Manufacturer: HP Inc.
Package Contents:

- Business Desktop ProDesk 400 G3 Desktop Computer
- Keyboard
- Windows 10 Pro License Media

Product Line: Business Desktop
Product Name: Business Desktop ProDesk 400 G3 Desktop Computer
Product Series: ProDesk 400 G3
Product Type: Desktop Computer

Interfaces/Ports

DisplayPort: Yes
Number of USB 2.0 Ports: 4
Number of USB 3.0 Ports: 4
Total Number of USB Ports: 8
VGA: Yes

Memory

Memory Technology: DDR4 SDRAM
Standard Memory: 4 GB

Miscellaneous

Environmental Certification: WEEE
Environmentally Friendly: Yes
Features: Security Slot
Form Factor: Small Form Factor
Green Compliance: ENERGY STAR
Certificate/Authority:
EPEAT Gold
REACH
WEEE
Green Compliant: Yes

Package Contents:

- Business Desktop ProDesk 400 G3 Desktop Computer

- Keyboard
- Windows 10 Pro License Media

Physical Characteristics

Depth:	299.7 mm
Form Factor:	Small Form Factor
Height:	269.2 mm
Weight (Approximate):	4.45 kg
Width:	94 mm

Power Description

Input Voltage:	120 V AC
----------------	----------

Processor & Chipset

Processor Generation:	6th Gen
Processor Manufacturer:	Intel
Processor Model:	i3-6100
Processor Speed:	3.70 GHz
Processor Type:	Core i3

Product Information

Features:	Security Slot
Form Factor:	Small Form Factor
Operating System Platform:	Windows
Width:	94 mm

Software

Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 7 Professional

Storage

Features:	Security Slot
Optical Drive Type:	DVD-Writer
Optical Media Supported:	DVD-RAM/±R/±RW
Total Hard Drive Capacity:	500 GB

Technical Information

Features:	Security Slot
Memory Technology:	DDR4 SDRAM
Operating System:	Windows 7 Professional
Optical Drive Type:	DVD-Writer
Optical Media Supported:	DVD-RAM/±R/±RW
Processor Generation:	6th Gen
Processor Manufacturer:	Intel

Video

Graphics Controller Manufacturer:	Intel
Graphics Controller Model:	HD Graphics 530
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM

Warranty

Limited Warranty:	1 Year
-------------------	--------

Wireless Specifications

Features:	Security Slot
-----------	---------------